

K-36

Class I, Div. 1 and 2
Groups B,C,D
Class II, Div. 1 and 2 Groups E,F,G
Class III
NEMA 4,7BCD,9EFG

ACSEW Control Operators: Accessories

	Item	Description	Catalog No.
	360° Rotating Shaft	Manual operated shaft used for devices requiring external adjustment. The shaft is 1/4" diameter and is provided with a coupling to compensate for misalignment.	ARO250C
	Standard Reset Button	Six inch length can be field modified for specific length. Suitable for use in Class I, Groups B, C & D applications. Add -L for long barrel.	AEPRS
	Miniature Reset Button	Six inch length can be field modified for specific length. Suitable for use in Class I, Groups B, C & D applications. 3/8 - 16 Threads.	AEPRM
	Weather Cap	Field attachable weather cap snaps on easily without the use of adhesives. Type AWL for pilot lights or lighted push buttons devices. Type AWP for push button devices.	AWL AWP
	Plug	3/4" NPSM to plug unused openings.	AA-9400
 <p data-bbox="138 1690 203 1722">APO2</p> <p data-bbox="389 1753 454 1785">APO1</p>	Potentiometer Operator	Operator for use with potentiometers having a 1/4" diameter by 7/8" long shaft. The operator is furnished with a control knob and dial plate marked 0 to 100. Use Long bushing (APO2) for applications where enclosure cover thickness is greater than 7/8".	APO1 APO2

NOTE: Use long barrel devices on enclosure applications with cover thickness exceeding 7/8 inch. See options page for legend plates. All Operators are 3/4" NPSM, except when specified otherwise.