

# BKX Round Junction Boxes

## CEC:

Class II, Division 1 and 2, Groups E, F, G

Class III

CSA Enclosure 4

## Applications

- Serve as pulling fittings.
- Provides openings for splicing.
- Connect and change direction of conduit runs.
- When used with a gasket, BKX junction boxes are weatherproof.
- BKX junction boxes are dust-ignitionproof when supplied for Class II applications. Suitable for use in grain elevators, flour mills and other environments where dust presents a hazard.

## Features

- Malleable iron Unilets™ offer high tensile strength, ductility, corrosion resistance and impact and shock resistance.
- Copperfree aluminum Unilets™ are lightweight, self-oxidizing, self-renewing and offer a high corrosion resistance.
- Roomy interiors: more wiring space.
- Smooth, rounded integral bushing in each hub protects conductor insulation.
- Accurately tapped, tapered threads for tight, rigid joints and ground continuity.
- BKX Series
  - Enclosed and gasketed boxes when used with hub or blank covers provide CSA Type 4 fit.
  - Suitable for exposed or concealed installations.
  - Boss in rear of box allows for fifth entry, factory or field entries, 1/2" or 3/4".
  - Available in three inside depths: 1-1/2", 2-1/4" and 3".
  - Furnished with four tapped holes and two close-up plugs.
  - Available in gray iron and aluminum.
  - Cushion fixture hangers are enclosed and gasketed.
  - Available for Class II, Division 1 applications.
  - Can be fitted with terminal block.

## Standard Materials

- BKX junction boxes and cast covers: gray iron
- BKX-A junction boxes and cast aluminum covers: copperfree (max. 4/10 of 1%) aluminum
- BKX sheet metal covers: steel or aluminum
- Gaskets: neoprene or composition fiber

## Standard Finishes

- Boxes and covers: triple-coat — (1) zinc electroplate, (2) chromate and (3) epoxy powder coat

## Options

- Factory installed terminal block, add suffix **-CB** to catalog number

## CEC Certifications and Compliances

- CSA Standard: C22.2 No. 18.1
- CSA Certified: 013017

## Related Products

- For explosionproof junction boxes, see Enclosures and Junction Boxes.
- For Class II Fixture Hangers, See *Lighting*.



**BKX Junction Boxes.**  
Choice of three depths.



**BKX Class II Junction Boxes with covers and gasket.**

# BKX Round Junction Boxes

CEC:  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 CSA Enclosure 4

Description	Hub Size (Inches)	Catalog Number	
		Aluminum	Gray Iron
 <p><b>BKXS — 1-1/2" Inside Depth</b>                      Furnished with four tapped holes and 4" centers, two tapped holes on 3-1/2" centers, four tapped conduit entries and two close-up plugs.</p> <p>Order covers as separate item.</p>	1/2	<b>BKXS-1A</b>	<b>BKXS-1</b>
	3/4	<b>BKXS-2A</b>	<b>BKXS-2</b>
 <p><b>BKXM — 2-1/4" Inside Depth</b>                      Furnished with four tapped holes on 4" centers, two tapped holes on 3-1/2" centers, four tapped conduit entries and two close-up plugs.</p> <p>Order covers as separate item.</p>	1/2	<b>BKXM-1A</b>	<b>BKXM-1</b>
	3/4	<b>BKXM-2A</b>	<b>BKXM-2</b>
	1	<b>BKXM-3A</b>	<b>BKXM-3</b>
 <p><b>BKXD — 3" Inside Depth</b>                      Furnished with four tapped holes on 4" centers, two tapped holes on 3-1/2" centers, four tapped conduit entries and two close-up plugs.</p> <p>Order covers as a separate item.</p>	1/2	<b>BKXD-1A</b>	<b>BKXD-1</b>
	3/4	<b>BKXD-2A</b>	<b>BKXD-2</b>
	1	<b>BKXD-3A</b>	<b>BKXD-3</b>
<b>BKX Covers — Furnished with gasket and screws ①</b>			
 <p>Cast</p>	Blank	<b>CBK-GA</b>	<b>CBKG</b>
	1/2	<b>CBK-1GA</b>	<b>CBK-1G</b>
	3/4	<b>CBK-2GA</b>	<b>CBK-2G</b>
 <p>Stamped Sheet Metal (steel)</p>	Blank	<b>CB-A</b>	<b>CB</b>
 <p><b>BKX Gasket</b>                      Neoprene</p>		—	<b>BKG</b>
<b>JB — Flexible Fixture Hangers — Furnished with gasket and screws.</b>			
 <p><b>Ball Type</b>                      15° swing in all directions, supports 113.4 kg (250 lbs)</p>	1/2	—	<b>JBK-50-BS</b>
	3/4	—	<b>JBK-75-BS</b>
 <p><b>Cushion Type</b>                      Enclosed and gasketed – 8° swing in all directions. Cushions 18 kg (40 lb), supports 113.4 kg (250 lbs)</p>	1/2	—	<b>JBK-50-CS</b>
	3/4	—	<b>JBK-75-CS</b>

① Stamped sheet metal CB covers not supplied with gasket.