

Rigid Conduit and IMC Locknuts

NEC/CEC:
Listed for Ordinary Locations

Application

- Used to secure and ground conduits and fittings to enclosures.

Material

- Zinc plated steel or aluminum

NEC/CEC Certifications and Compliances

- UL Standard: 514B
- UL Listed: E-11853, E-24264
- CSA Standard: C22.2 No. 18.3
- CSA Certified: 065178
- NEMA: FB-1

	Trade Size (Inches)	Dimensions in Millimeters (Inches)		Weight per 100 kg (lb)	Appleton™ Catalog Number	O–Z/Gedney™ Catalog Number
		Diameter	Height			
	Locknuts — Steel					
	3/8	23.9 (0.94)	3.3 (0.13)	0.64 (1.40)	BL38	1–38S
	1/2	28.7 (1.13)	3.3 (0.13)	0.59 (1.30)	BL50	1–50S
	3/4	35.1 (1.38)	3.3 (0.13)	1.09 (2.40)	BL75	1–75S
	1	42.9 (1.69)	4.8 (0.19)	1.81 (4.00)	BL100	1–100S
	1-1/4	57.2 (2.25)	4.8 (0.19)	2.49 (5.50)	BL125	1–125S
	1-1/2	60.5 (2.38)	4.8 (0.19)	4.54 (10.00)	BL150	1–150S
	2	73.2 (2.88)	4.8 (0.19)	6.30 (13.90)	BL200	1–200S
	2 - 1/2	90.4 (3.56)	9.7 (0.38)	10.89 (24.00)	BL250	1–250
	3	108.0 (4.25)	9.7 (0.38)	14.51 (32.00)	BL300	1–300
	3 - 1/2	122.2 (4.81)	9.7 (0.38)	21.32 (47.00)	BL350	1–350
	4	138.2 (5.44)	9.7 (0.38)	27.22 (60.00)	BL400	1–400
	5	169.9 (6.69)	12.7 (0.50)	44.45 (98.00)	BL500	1–500
6	201.7 (7.94)	12.7 (0.50)	72.57 (160.00)	BL600	1–600	
	PVC Gasketed Sealing Locknuts — Steel — Liquidtight					
	1/2	28.7 (1.13)	6.4 (0.25)	0.64 (1.40)	BLSG50	SLG–50S
	3/4	35.3 (1.39)	6.4 (0.25)	1.18 (2.60)	BLSG75	SLG–75S
	1	44.5 (1.75)	7.1 (0.28)	2.27 (5.00)	BLSG100	SLG–100S
	1-1/4	53.1 (2.09)	7.1 (0.28)	3.08 (6.80)	BLSG125	SLG–125S
	1-1/2	61.2 (2.41)	7.1 (0.28)	5.22 (11.50)	BLSG150	SLG–150S
	2	74.7 (2.94)	7.9 (0.31)	6.67 (14.70)	BLSG200	SLG–200S
	2 - 1/2	88.9 (3.50)	9.7 (0.38)	10.89 (24.00)	BLSG250	SLG–250S
	3	106.4 (4.19)	9.7 (0.38)	14.51 (32.00)	BLSG300	SLG–300S
	3 - 1/2	120.7 (4.75)	11.2 (0.44)	21.32 (47.00)	BLSG350	SLG–350S
	4	135.6 (5.34)	11.2 (0.44)	27.22 (60.00)	BLSG400	SLG–400S ①
	5	168.4 (6.63)	12.7 (0.50)	44.45 (98.00)	BLSG500	—
	6	200.2 (7.88)	14.2 (0.56)	72.57 (160.00)	BLSG600	—

① Not UL or CSA certified

Rigid Conduit and IMC Locknuts

NEC/CEC:
Listed for Ordinary Locations

	Trade Size (Inches)	Dimensions in Millimeters (Inches)		Weight per 100 kg (lb)	Appleton™ Catalog Number	O–Z/Gedney™ Catalog Number
		Diameter	Height			
Bonding Locknuts — Steel						
	1/2	35.1 (1.38)	4.8 (0.19)	1.36 (3.00)	GL50	101
	3/4	41.4 (1.63)	4.8 (0.19)	1.36 (3.00)	GL75	102
	1	46.0 (1.81)	6.4 (0.25)	2.27 (5.00)	GL100	103
	1-1/4	58.7 (2.31)	6.4 (0.25)	2.72 (6.00)	GL125	104
	1-1/2	66.8 (2.63)	6.4 (0.25)	3.18 (7.00)	GL150	105
	2	79.5 (3.13)	6.4 (0.25)	5.90 (13.00)	GL200	106
	2 - 1/2	90.4 (3.56)	11.2 (0.44)	8.16 (18.00)	GL250	107
	3	108.0 (4.25)	11.2 (0.44)	16.78 (37.00)	GL300	108
	3 - 1/2	122.2 (4.81)	12.7 (0.50)	20.41 (45.00)	GL350	109
	4	138.2 (5.44)	12.7 (0.50)	22.68 (50.00)	GL400	110
	5	177.8 (7.0)	12.7 (0.5)	78.26 (35.50)	—	112 ①
	6	206.5 (8.13)	12.7 (0.5)	103.05 (46.70)	—	113 ①
Locknuts — Aluminum						
	1/2	28.7 (1.13)	4.8 (0.19)	0.23 (0.50)	BL50A	1–50A
	3/4	35.1 (1.38)	4.8 (0.19)	0.36 (0.80)	BL75A	1–75A
	1	42.9 (1.69)	4.8 (0.19)	0.73 (1.60)	BL100A	1–100A
	1-1/4	57.2 (2.25)	4.8 (0.19)	1.32 (2.90)	BL125A	1–125A
	1-1/2	60.5 (2.38)	4.8 (0.19)	1.00 (2.20)	BL150A	1–150A
	2	73.2 (2.88)	4.8 (0.19)	2.18 (4.80)	BL200A	1–200A
	2 - 1/2	90.4 (3.56)	9.7 (0.38)	3.40 (7.50)	BL250A	1–250A
	3	108.0 (4.25)	9.7 (0.38)	4.81 (10.60)	BL300A	1–300A
	3 - 1/2	122.2 (4.81)	9.7 (0.38)	6.49 (14.30)	BL350A	1–350A
	4	138.2 (5.44)	9.7 (0.38)	8.44 (18.60)	BL400A	1–400A
	5	12.7 (0.5)	169.93 (6.69)	13.70 (30.20)	—	1–500A
	6	12.7 (0.5)	201.68 (7.94)	40.12 (18.20)	—	1–600A

① Not UL or CSA certified