

# PLG Close-Up Plugs and BR Reducers

## Explosionproof, Dust-Ignitionproof

UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.

### NEC/CEC:

Class I, Division 1 and 2, Groups A Ⓢ, B Ⓢ, C, D

Class II, Division 1 and 2, Groups E, F, G

Class III

HAZARDOUS LOCATION FITTINGS: NEC/CEC EXPLOSIONPROOF CONDUIT FITTINGS

APPLETON™

|  | NPT Threads<br>Size (Inches) | Catalog Number     |                          |                           |
|--|------------------------------|--------------------|--------------------------|---------------------------|
|  |                              | Steel (1/2" to 1") | Malleable (1-1/4" to 6") | Aluminium<br>(1/2" to 4") |
| <b>PLG – Close-Up Plugs</b>  |                              |                    |                          |                           |
| <br>Recessed Head | <i>Recessed Head</i>         |                    |                          |                           |
|  | 1/2                          | PLG-50R Ⓢ Ⓢ        | —                        | PLG-50RA Ⓢ Ⓢ              |
|  | 3/4                          | PLG-75R Ⓢ Ⓢ        | —                        | PLG-75RA Ⓢ Ⓢ              |
|  | 1                            | PLG-100R Ⓢ Ⓢ       | —                        | PLG-100RA Ⓢ Ⓢ             |
|  | 1-1/4                        | —                  | PLG-125 Ⓢ Ⓢ              | PLG-125A Ⓢ Ⓢ              |
|  | 1-1/2                        | —                  | PLG-150 Ⓢ Ⓢ              | PLG-150A Ⓢ Ⓢ              |
|  | 2                            | —                  | PLG-200 Ⓢ Ⓢ              | PLG-200A Ⓢ Ⓢ              |
|  | 2-1/2                        | —                  | PLG-250 Ⓢ Ⓢ              | PLG-250A Ⓢ Ⓢ              |
| <br>Square Head   | <i>Square Head</i>           |                    |                          |                           |
|  | 1/2                          | PLG-50S Ⓢ          | —                        | —                         |
|  | 3/4                          | PLG-75S Ⓢ          | —                        | —                         |
|  | 1                            | PLG-100S Ⓢ         | —                        | —                         |
|  | 1-1/4                        | —                  | PLG-125S Ⓢ               | —                         |
|  | 1-1/2                        | —                  | PLG-150S Ⓢ               | —                         |
|  | 2                            | —                  | PLG-200S Ⓢ               | —                         |
|  | 2-1/2                        | —                  | PLG-250S Ⓢ               | —                         |
| <br>Bar Head    | <i>Bar Head (Cast Iron)</i>  |                    |                          |                           |
|  | 3                            | —                  | PLG-300S Ⓢ               | —                         |
|  | 3-1/2                        | —                  | PLG-350S Ⓢ               | —                         |
|  | 4                            | —                  | PLG-400S Ⓢ               | —                         |
|  | 5                            | —                  | PLG-500B                 | —                         |
|  | 6                            | —                  | PLG-600B                 | —                         |

|   | Large Hub Size<br>(Inches) | Small Hub Size<br>(Inches) | Catalog Number |             |
|---|----------------------------|----------------------------|----------------|-------------|
|   |                            |                            | Malleable      | Aluminium   |
| <b>BR – Threaded Bell Reducing Couplings</b>  |                            |                            |                |             |
|  | 3/4                        | 1/2                        | BR75-50 Ⓢ      | BR75-50A Ⓢ  |
|   | 1                          | 1/2                        | BR100-50 Ⓢ     | BR100-50A Ⓢ |
|   | 1                          | 3/4                        | BR100-75 Ⓢ     | BR100-75A Ⓢ |
|   | 1                          | 1                          | BR125-100 Ⓢ    | BR125-100A  |
|   | 1-1/4                      | 3/4                        | BR125-75 Ⓢ     | BR125-75A   |
|   | 1-1/2                      | 1                          | BR150-100 Ⓢ    | BR150-100A  |
|   | 1-1/2                      | 3/4                        | BR150-75 Ⓢ     | BR150-75A   |
|   | 1-1/2                      | 1-1/4                      | BR150-125 Ⓢ    | BR150-125A  |
|   | 2                          | 3/4                        | BR200-75 Ⓢ     | BR200-75A   |
|   | 2                          | 1                          | BR200-100 Ⓢ    | BR200-100A  |
|   | 2                          | 1-1/4                      | BR200-125 Ⓢ    | BR200-125A  |
|   | 2                          | 1-1/2                      | BR200-150 Ⓢ    | BR200-150A  |
|   | 2-1/2                      | 1-1/2                      | BR250-150 Ⓢ    | BR250-150A  |
|   | 3                          | 2                          | BR300-200 Ⓢ    | BR300-200A  |
|   | 3-1/2                      | 2-1/2                      | BR350-250 Ⓢ    | BR350-250A  |
| 4   | 3                          | BR400-300 Ⓢ                | BR400-300A     |             |
| 5   | 4                          | BR500-400                  | BR500-400A     |             |

Ⓢ Urethane paint available on select items. Add suffix **-UP** to catalog number.

Ⓢ Indicates items in the shaded area which are UL Listed for Class I, Groups A, B, C, D; Class II, Groups E, F, G; and Class III.

Ⓢ Indicates items are UL Listed for Class I, Groups B, C, D; Class II, Groups E, F, G; and Class III.