

Code•Master™ 2 HID Factory Sealed Floodlights

Marine (Outside Type). Explosionproof

Integrally Ballasted. 250 W, 400 W HPS; 150 W, 175 W, 250 W, 400 W PSMH; 175 W, 250 W, 400 W MH. Mogul Base.

NEC:
Class 1, Division 1 and 2, Groups C, D
Marine Type Electric Fixtures
Outside Type (Salt Water)

CEC:
Class I, Division 1 and 2, Groups B, C, D
Class II, Division 1, Groups E, F, G
Class II, Division 2, Groups F, G
Class III
CSA 4X

Lamp	Watts	Volts	High Pressure Sodium ①		Ballast Amps Pulse Start Metal Halide Super CWA		Metal Halide CWA		Fuse Quantity Required	Fuse Kit Catalog Number		
			Start	Operating	Start	Operating	Start	Operating		HPS	PSMH	MH ②
150	120		2.00	1.70	—	—	—	—	1	CF-10	—	—
	208		1.15	0.95	—	—	—	—	2	CF-5	—	—
	240		1.00	0.85	—	—	—	—	2	CF-5	—	—
	277		0.88	0.72	—	—	—	—	1	CF-5	—	—
	347		0.52	0.56	—	—	—	—	1	CF-5	—	—
	480		0.50	0.47	—	—	—	—	2	CF-3	—	—
175	120		—	—	0.80	1.80	1.30	1.80	1	—	CF-5	CF-5
	208		—	—	0.50	1.00	0.75	1.10	2	—	CF-3	CF-3
	240		—	—	0.40	0.90	0.65	0.90	2	—	CF-3	CF-3
	277		—	—	0.40	0.80	0.55	0.80	1	—	CF-2	CF-2
	347		—	—	0.25	0.65	0.50	0.65	1	—	CF-2	CF-2
	480		—	—	0.15	0.45	—	—	2	—	CF-3	—
250	120		2.00	2.80	2.00	2.30	1.20	2.60	1	CF-8	CF-10	CF-8
	208		1.20	1.50	1.10	1.40	0.65	1.50	2	CF-5	CF-6	CF-5
	240		1.00	1.30	1.00	1.20	0.60	1.30	2	CF-5	CF-6	CF-5
	277		0.85	1.10	0.80	1.00	0.50	1.12	1	CF-5	CF-5	CF-3
	347		0.60	0.93	0.62	0.90	0.80	0.90	1	CF-5	CF-3	CF-3
	480		0.40	0.65	0.30	0.60	—	—	2	CF-2	CF-3	—
400	120		3.30	3.80	3.10	3.70	3.25	4.00	1	CF-15	CF-12	CF-10
	208		1.80	2.20	1.70	2.10	1.90	2.30	2	CF-8	CF-6	CF-8
	240		1.60	1.90	1.50	1.90	1.65	2.00	2	CF-8	CF-6	CF-5
	277		1.40	1.70	1.30	1.60	1.40	1.75	1	CF-5	CF-5	CF-5
	347		1.00	1.32	1.10	1.35	1.20	1.40	1	CF-5	CF-5	CF-5
	480		0.80	1.00	0.80	0.95	—	—	2	CF-5	CF-3	—

Fuse Kit includes fuse, fuse holder and necessary hardware for field installation. Mounts easily in ballast body with one screw. Order one fuse for 120 and 277 V, and 2 fuses for 208, 240 and 480 V. CF-2 = 2 amp; CF-3 = 3 amp; CF-5 = 5 amp; CF-6 = 6 amp; CF-8 = 8 amp; CF-10 = 10 amp; CF-12 = 12 amp

① 50 through 150 W HPS have H.P.F. High Reactance ballasts; 250 W and 400 W HPS have CWA ballasts.

② Mercury vapor and metal halide luminaires are not available for purchase within the United States. Please check with your countries governing legislation regarding allowable lamp types before ordering.