

ELS Series Emergency Lighting System Accessories

Explosionproof, Dust-Ignitionproof

Remote and direct mounted fixtures for hazardous location applications

	Description	Catalog Number
Guard		
		AAGU1
Three-Way Exit Sign		
	Epoxy enameled steel — 6”-high red lettering Mounts to fixture units in place of guard.	CJEXRN
Single-Sided Exit Sign		
	Epoxy enameled steel — 6”-high red lettering Mounts to fixture units in place of guard.	AEXR-15R
30° Angle Reflector		
		AARW15AN
Standard Dome Reflector		
		AARW15ST
Push-to-Test Station		
	Complete Push-to-Test Station Cover with Switch and Pilot Light Switch Only Pilot Light Only Lamp, 18 W, 6 Vdc Lamp, 28 W, 6 Vdc Lamp, 18 W, 12 Vdc Lamp, 28 W, 12 Vdc	EFDCB150J1U1-T-A EFKB-J1U1-TEST SPBB-U1-Q SPLNS-RE-B 59620527074 59620527075 59620527076 59620527078

Lighting

LIGHTING: EXPLOSIONPROOF — EMERGENCY