

EFU Fluorescent Factory Sealed Luminaires

Explosionproof, Dust-Ignitionproof

UNILETS® for use with Threaded Metal Conduit Suitable for use in Wet Locations

NEC/CEC:

Class I, Division 1 and 2, Groups C, D
Class II, Division 1 and 2, Groups E, F, G
Class III

	Lamp	Volts	Hub Size (Inches)	Temperature Rating	Supply Wire °C (°F)	Catalog Number ②
Two Lamps						
	32 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS232-BU ①
	T8 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS232-347 ③①
	1.22 m (4') 265MA					
	40 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS240-BU ①
	T12 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS240-347 ③①
	1.22 m (4') 430MA					
	60 W					
	Rapid Start High Output	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	AH260-BU
T-12 Recessed Double Contact	347 V, 60 Hz	3/4	T-6	60 (140)	AH260-347 ③	
1.22 m (4') 800MA						
110 W						
Rapid Start VHO-SHO	120 V, 60 Hz	3/4	T-6	60 (140)	AVH210-118	
T-12 Recessed Double Contact	277 V, 60 Hz	3/4	T-6	60 (140)	AVH210-277	
1.22 m (4') 1500MA	347 V, 60 Hz	3/4	T-6	60 (140)	AVH210-347 ③	
Three Lamps						
	32 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS332-BU ①
	T8 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS332-347 ③①
	1.22 m (4') 265MA					
	40 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS340-BU
	T12 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS340-347 ③
	1.22 m (4') 430MA					
	60 W					
	Rapid Start High Output	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	AH360-BU
T-12 Recessed Double Contact	347 V, 60 Hz	3/4	T-6	60 (140)	AH360-347 ③	
1.22 m (4') 800MA						
Four Lamps						
	32 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS432-BU ①
	T8 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS432-347 ③①
	1.22 m (4') 265MA					
	40 W					
	Rapid Start	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	ARS440-BU
	T12 Bi-Pin	347 V, 60 Hz	3/4	T-6	60 (140)	ARS440-347 ③
	1.22 m (4') 430MA					
	60 W					
	Rapid Start High Output	120-277 V, 50/60 Hz	3/4	T-6	60 (140)	AH460-BU
T-12 Recessed Double Contact	347 V, 60 Hz	3/4	T-6	60 (140)	AH460-347 ③	
1.22 m (4') 800MA						
110 W						
Rapid Start Very High Output	120 V, 60 Hz	3/4	T-6	60 (140)	AVH410-118	
T-12 Recessed Double Contact	277 V, 60 Hz	3/4	T-6	60 (140)	AVH410-277	
1.22 m (4') 1500MA	347 V, 60 Hz	3/4	T-6	60 (140)	AVH410-347 ③	
Protector for two-lamp fluorescent fixture						
	Fits two lamp 1.22 m (4') fixtures only (ARS, AH and AVH series) UV stabilized polycarbonate					EFP248
	Wire guard— use 1 piece for 2 lamp fixtures, 2 pieces for 4 lamp fixtures (not available for 3 lamp fixtures)					ARSGUSS

NOTE: In paint spray areas, solvents and thinners may "cloud" the polycarbonate. Light transmission characteristics may be reduced.

① For Emergency Battery Pack, add suffix -EL.

② Fluorescent lamps are not included. Supplied with automatic resetting dual protected "Class P" ballast. For additional external fusing, add suffix -F.

③ Certified to meet the Canadian Electrical Code (CEC) only.

Visit our website at www.emerson.com or contact us at (800) 621-1506.

© May 2016

Appleton

FLUORESCENT/AREA: NEC/CEC EXPLOSIONPROOF