

# U-Line™ Factory Sealed 20 Amp Malleable Iron Receptacles

## Explosionproof, Dust-Ignitionproof

125 Vac, 20 Amp, 1 HP; 250 Vac, 20 Amp, 2 HP. Dead-Front Safety Construction.

**NEC/CEC:**

Class I, Division 1 Groups B<sup>+</sup>, C, D  
 Class I, Division 2 Groups B, C, D  
 Class II, Division 1 and 2 Groups F, G  
 Class III  
 NEMA 3, 3R

### Malleable Iron Receptacle and Malleable Iron Mounting Box

Type	Wire/Pole	Hub Size (Inches)	Catalog Number		
			125 Vac, 1 HP 	250 Vac, 2 HP 	
<b>Two Gang</b>					
<i>Class I, Division 1 and 2 Groups C, D; Class I, Division 2, Groups B, C, D; Class II, Division 1 and 2 Groups F, G; Class III.</i>					
	Dead-End	2W, 3P	1/2	EFS250-2023M	EFS250-20232M
			3/4	EFS275-2023M	EFS275-20232M
			1	EFS210-2023M	EFS210-20232M
	Feed-Thru	2W, 3P	1/2	EFSC250-2023M	EFSC250-20232M
			3/4	EFSC275-2023M	EFSC275-20232M
			1	EFSC210-2023M	EFSC210-20232M
Dead-End	Feed-Thru				

### Malleable Iron Replacement Receptacle Only

	2W, 3P	EFSR-2023M	EFSR-20232M
	Spring door replacement assembly (iron)	ULSCM	

◆ Select items suitable for Class I, Group B, C and D; Class II, Groups F, G; and Class III. See product selection pages for suitable items.