

EYDM 25% * Fill Vertical Conduit Drain Sealing Fittings

For Close Turning Radius. Explosionproof, Dust-Ignitionproof, Raintight.

UNILETS™ for Use with Threaded Rigid Metal Conduit and IMC.


NEC/CEC:

Class I, Division 1 and 2, Groups B♦, C, D


Class II, Division 1 and 2, Groups E, F, G

Class III

	Trade Size (Inches)	Centimeters (Inches)			Kwiko™ A Cement Required Grams (Ounces)	Catalog Number	
		A (Length)	B (Width)	Turning Radius ①		Malleable Iron	Almag 35 Aluminum
EYDM Vertical Conduit Drain Seals for Close Turning Radius (25% fill) ‡							
Male/Female (Removable Male Nipple)							
 1/2" — 1"	1/2	8.3 (3.28)	3.2 (1.25)	4.1 (1.63)	56.7 (2.00)	EYDM-50 ♦	EYDM-50AL
	3/4	9.4 (3.69)	3.8 (1.25)	4.9 (1.91)	56.7 (2.00)	EYDM-75 ♦	EYDM-75AL
	1	10.9 (4.31)	4.4 (1.75)	6.0 (2.38)	85.1 (3.00)	EYDM-100 ♦	EYDM-100AL
 1-1/4" — 3"	1-1/4	12.9 (5.06)	5.6 (2.19)	4.5 (1.75)	198.4 (7.00)	EYDM-125 ♦	EYDM-125AL
	1-1/2	14.0 (5.50)	6.2 (2.44)	5.2 (2.06)	368.5 (13.00)	EYDM-150 ♦	EYDM-150AL
	2	15.8 (6.25)	7.6 (3.00)	5.9 (2.31)	623.7 (22.00)	EYDM-200 ♦	EYDM-200AL
 3-1/2" — 4"	2-1/2	19.1 (7.50)	8.9 (3.50)	6.8 (2.69)	1020.6 (36.00)	EYDM-250 ♦	EYDM-250AL
	3	21.6 (8.50)	10.8 (4.25)	8.4 (3.31)	1729.3 (61.00)	EYDM-300 ♦	EYDM-300AL
	3-1/2	23.3 (9.19)	12.1 (4.75)	8.6 (3.41)	2523.1 (89.00)	EYDM-350 ♦	EYDM-350AL
	4	24.8 (9.75)	13.3 (5.22)	9.4 (3.69)	3231.8 (14.00)	EYDM-400 ♦	EYDM-400AL



EYDM
1/2" — 1"



EYDM
1-1/4" — 4"

* Per NEC 501.15(C)(6), seals in Class I, Division 1 and 2 must be limited to conductor fill of 25% of cross sectional area of a rigid metal conduit of the same trade size unless approved for higher percentage fill. See 40% fill sealing fittings.

① Turning radius with cover or plug removed.

♦ Indicated items in the shaded area which are UL Listed for Class I, Groups B, C, D; Class II, Groups E, F, G; and Class III.