

FH and FHSN Series Flexible Fixture Hangers

Hook and Loop

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

CEC:

Listed for Ordinary (Unclassified) Locations

Applications

- Designed for suspension of HID, fluorescent and incandescent lighting fixtures.

Features

- Protect fixture against wind and vibration damage.
- Cushion type for added protection where lighting fixtures are subjected to vibration.
- Malleable iron for strength and safety.
- Hook and loop combination permits quick disconnect and removal of fixture for maintenance.
- Offer inexpensive means of pendant flexible suspension of lighting fixtures.
- Permit free swing in any direction.
- EF and FHSN jaw openings can be completely closed for added safety.

Standard Materials

- Malleable iron

Standard Finishes

- Zinc electroplate and clear chromate

CEC Certifications and Compliances

- CSA Certified: 065180



FHLM



FHHM



FHSN

Illustrated Features



GHBPH power hook comes with supplied receptacle, twistlock plug, cable and FHLM fixture loop.



FHLM fixture loop installed in pendant hood and used with GHBPH series powerhook.

POLES/HANGERS: NEC/CEC ORDINARY LOCATION FLEXIBLE FIXTURE HANGERS

Appleton®

FH and FHSN Series Flexible Fixture Hangers

Hook and Loop

UNILETS® for Use with Threaded Rigid Metal Conduit and IMC.

CEC:
Listed for Ordinary (Unclassified) Locations

	Size (Inches)	Length A (mm) in	Support Weight kg (lbs)	Catalog Number
FH — Hanger Loops — With 5/8" diameter wireway				
 FHLM	FHLM — Male			
	1/2	98.6 (3.88)	157.5 (350)	FHLM-50
	3/4	104.9 (4.13)		FHLM-75
	 FHLF	FHLF — Female		
1/2		82.6 (3.25)	157.5 (350)	FHLF-50
3/4		82.6 (3.25)		FHLF-75
FH — Hanger Hooks — With 5/8" diameter wireway, 3/8" jaw opening				
 FHMM	FHMM — Male			
	1/2	98.6 (3.88)	90.0 (200)	FHMM-50
	3/4	104.9 (4.13)		FHMM-75
	 FHMF	FHMF — Female		
1/2		82.6 (3.25)	90.0 (200)	FHMF-50
3/4		82.6 (3.25)		FHMF-75
FH — Hanger Hooks — With 5/8" diameter wireway, 3/8" jaw opening, safety screw				
 FHMM	FHMM — Male			
	1/2	98.6 (3.88)	34.0 (75)	FHMM-50-SS
	3/4	104.9 (4.13)		FHMM-75-SS
	 FHMF	FHMF — Female		
1/2		82.6 (3.25)	34.0 (75)	FHMF-50-SS
3/4		82.6 (3.25)		FHMF-75-SS
FHHCG — Gasketed Fixture Hanger Hook — With 5/8" wire opening, 3/8" jaw opening, safety screw — As FHMM's above, with internal grommet to prevent moisture and dirt entry				
 FHHCG	FHHCG — Male			
	1/2	108.0 (4.25)	34.0 (75)	FHHCG-3750-SS
	3/4	108.0 (4.25)		FHHCG-3775-SS
	FHSN — Conduit Suspension Hanger — With safety strap — clamps around rigid conduit or IMC — Has 3/8" jaw opening			
 FHSN	1/2	79.5 (3.13)	67.5 (150)	FHSN-50
	3/4	82.6 (3.25)		FHSN-75
	1	85.9 (3.38)		FHSN-100