

ATX™ FL Series Light Duty Nonmetallic Fluorescent Luminaires

Standard and Emergency Back-Up. Zone 2 and 22

ATEX:
Zone 2 and 22
II 3 GD
ATEX - IEC IP65/67

FLUORESCENT/AREA: ATEX/IECex STANDARD AND EMERGENCY BACK-UP

Standard Version for Armored and Unarmored Cable

Supplied with one M20 cable entry at each end plus two locknuts, two earth continuity and one blanking plug.
Also supplied with one 2 x 3 x 2.5 mm² (0.004 x 0.003 in²) max. flexible or rigid connection terminal block.

Number of Lamps	Watts	Voltage (V)	Weight kg (lbs)	Volume dm ³ (in ³)	Pack.	Catalog Number
1	18	220/240	2.3 (5.07)	22.3 (1360.83)	1	FLB118BKSA
2	18	220/240	2.3 (5.07)	22.3 (1360.83)	1	FLB218BKSA
2	18	110/254	2.3 (5.07)	22.3 (1360.83)	1	FLB218BUSA
1	36	220/240	2.8 (6.17)	38.0 (2318.90)	1	FLB136BKSA
1	36	110/254	2.8 (6.17)	38.0 (2318.90)	1	FLB136BUSA
2	36	220/240	3.6 (7.94)	38.0 (2318.90)	1	FLB236BKSA
2	36	110/254	3.6 (7.94)	38.0 (2318.90)	1	FLB236BUSA
1	58	220/240	3.4 (7.50)	45.0 (2746.07)	1	FLB158BKSA
1	58	110/254	3.4 (7.50)	45.0 (2746.07)	1	FLB158BUSA
2	58	220/240	4.4 (9.70)	45.0 (2746.07)	1	FLB258BKSA
2	58	110/254	4.4 (9.70)	45.0 (2746.07)	1	FLB258BUSA

Emergency Version for Armored and Unarmored Cable

Supplied with one M20 entries with earth continuity at each end. Also supplied with two M20 locknuts and one blanking plug.
Equipped with one 2 x (5 x 2.5 mm² / 0.008 x 0.003 in²) max. flexible or rigid connection terminal block

Number of Lamps	Watts	Voltage (V)	Weight kg (lbs)	Volume dm ³ (in ³)	Pack.	Catalog Number
2	18	110/254	4.5 (9.92)	22.3 (1360.83)	1	FLB218BUSAE
2	36	110/254	7.0 (15.4)	38.0 (2318.90)	1	FLB236BUSAE
2	58	110/254	7.5 (16.53)	45.0 (2746.07)	1	FLB258BUSAE