


Areaster™ 1000 Integrally Ballasted Floodlights

1000 W and 1500 W HID

Ordinary Location. NOT available for use in CEC governed locations

NEC: Rated for Ordinary (Unclassified) Locations

	Description	Catalog Numbers
<p>Crossarm Mounting Bracket</p> 	<p>Has 180° horizontal adjustment — degree marked. Facilitates mounting floodlight to crossarm or other flat surface, or to G-AM-8-WB. Includes floodlight yoke bolts. Malleable iron, zinc plated, chromate sealed, architectural bronze polyester finish.</p>	<p>G-AM-8-CA</p>
<p>Pipe or Wall Mount Bracket</p> 	<p>Used with G-AM-8-CA. Clamps to 1" to 2-1/2" pipe, vertical or horizontal, or mounts on flat surfaces. Includes U-bolt and crossarm bracket bolts. Malleable iron, zinc plated, chromate sealed, with architectural bronze polyester finish.</p>	<p>G-AM-8-WB</p>
<p>Poletop Slip-Fitter</p> 	<p>Slip-fits 1-1/2" or 2" pipe size poletop tenons. Includes floodlight yoke bolts, 3 locking bolts, and cord grip. Body is malleable iron-zinc plated, chromate sealed, with cast aluminum cap. Assembly has architectural bronze polyester finish.</p>	<p>G-SF20</p>
	<p>Slip-fits 2" or 2-1/2" poletop tenons. Includes floodlight yoke bolts, 3 locking bolts, and cord grip. Malleable iron, zinc plated, chromate sealed, with architectural bronze polyester finish.</p>	<p>G-AM-8-SF</p>
<p>Locking-Type Photocontrol Receptacle</p> 	<p>For NEMA type photocontrol, with installation hardware and instructions.</p>	<p>G-1PCR</p>
<p>Vandal Shield</p> 	<p>UV stabilized polycarbonate, with installation hardware and instructions.</p>	<p>G-AM-8-NVS</p>
<p>Top Visor</p> 	<p>Easy to install with hardware supplied. Aluminum, with architectural bronze polyester finish.</p>	<p>G-AM-6-NV</p>

HID Luminaires | Floodlight | Ordinary Location | NEC / CEC