

Contender™ CPS Factory Sealed 20 Amp Pin and Sleeve Receptacles

Explosionproof, Delayed Action

NEC/CEC:
Class I, Division 1 and 2, Groups C, D

Does not intermate with
CPS 20 Amp Factory Sealed Pin
and Sleeve Receptacles

		Type	Wire/Pole	Plug Cable Diameter (Inches)	Catalog Numbers ① 20 Amp 125–250 Vac 1HP, 20 Amp @ 18 Vdc
Cover Assemblies					
		Receptacle with Spring Cover Only			CPS152R
		GFCI Cover, 5 mA Trip Setting ②			GFS1
CPS152R	GFS1				
<hr/>					
		Spring Cover Replacement Kit (Aluminum)			CPSCA
CPSCA					
<hr/>					
Plug		Pressure Terminals	2W, 3P	0.538 to 0.639	CPP516
		Plug amperes match receptacle ratings			

APPLETON™

PLUGS AND RECEPTACLES: NEC/CEC HAZARDOUS LOCATION

① Aluminum receptacle cover and malleable iron EDS box. For aluminum box and receptacle cover, add suffix **-SA**.

② GFI units rated 20 Amp, 125 Vac.

Note: Appleton Contender CPS Receptacles are UL Classified for use with Crouse-Hinds CPP516 plug.