

# V-51™ Incandescent Luminaires

Enclosed and Gasketed. UNILETS® for use with threaded metal conduit.  
Hazardous Location. Suitable for use in wet locations. ①

NEC: Class I, Division 2, Groups A, B, C, D  
CEC: Class I, Division 2, Groups A, B, C, D | Class II, Divisions 1 and 2, Groups E, F, G ② | Class III | Enclosure 3R

Wall	Ceiling	Type	Catalog Numbers — Malleable Iron
<b>Wall and Ceiling Outlet Box Mounting Hoods</b>			
<b>SEH ③ and 3-1/4" or 4" Octagonal Outlet Box Mounting ④ for Non-Classified Areas Only</b>			
		Wall ⑤	0BVW1
		Ceiling	0BV1
<b>GS Round Base Outlet Box Mounting – Form 20 ③</b>			
		Wall ⑤	GSW2
		Ceiling	GS2
<b>JB Round Base Outlet Box Mounting ③</b>			
		Wall ⑤	JBW1
		Ceiling	JB1

A21	PS30	Type	Lamp Watts	Catalog Numbers — Malleable Iron
<b>Fixture Units</b>				
<b>Adapter/Socket, Globe and Guard</b>				
		A21	60-150	VU100M
		PS30	150-300	VU200M
<b>Adapter/Socket and Globe</b>				
		A21	60-150	VU100MLG
		PS30	150-300	VU200MLG
<b>Adapter/Socket</b>				
		A21	60-150	VAD-1M ⑥
		PS30	150-300	VAD-2M ⑥

① With heat-resistant glass globes or plastic globes.

② 300 W PS-25 not approved for Class II, Division 1 and 2, Group G; Class III.

③ Cast outlet boxes and gaskets are available in the Fitting Section. Screws, gasket and adapter plate furnished with fixture mounting hood.

④ Octagonal outlet boxes are available in the Commercial Fitting Section. Screws, gasket and adapter plate furnished with fixture mounting hood.

⑤ Mounting hoods for wall installations can only be used with 30° angle reflectors.

⑥ Accepts steel wire guard only.