

# GS Conduit Outlet Boxes, Covers and Hangers

UNILETS™ for use with Threaded Rigid Metal Conduit and IMC.

**NEC:**  
Rated for Ordinary Locations

## Applications

- Serve as pulling fittings.
- Provides openings for splicing.
- Connect and change direction of conduit runs.
- When used with a gasket, GS junction boxes are weatherproof.

## Features

- Raintight when enclosed and gasketed with hub or blank covers.
- Extra wide mating surfaces of GS box and cover provide greater gasket contact for more positive seal.
- GSU-20 accommodates connection block.
- Universal design — furnished with 4 threaded universal 3/4" hubs, four 3/4" to 1/2" reducers, and three 1/2" close-up plugs.
- Furnished with mounting lugs.
- Cushion fixture hangers are enclosed and gasketed.

## Standard Materials


- Conduit outlet boxes, covers and fixture hangers: malleable iron
- Gaskets: neoprene

## Standard Finishes

- Malleable iron conduit outlet boxes and covers: triple-coat — (1) zinc electroplate, (2) chromate and (3) epoxy powder coat

## NEC Certifications and Compliances

- UL Standard: 514A

	Description	Hub Size (Inches)	Depth in Millimeters (Inches) (A)	Catalog Number
	<b>GS — 1-3/4" Inside Depth, with mounting lugs — Form 20</b>			
	Four threaded universal 3/4" hubs, four 3/4" to 1/2" reducers, and three 1/2" close-up plugs.	1/2 or 3/4	—	<b>GSU-20</b>
	Four 1" threaded openings and three 1" close-up plugs.	1	—	<b>GSU-100</b>
	<b>GS — Cast Covers — Furnished with gasket and screws. Enclosed and gasketed for raintight fit, supports 113.4 kg (250 lb)</b>			
	Hub Cover	1/2	44.5 (1.75)	<b>GSK-50-20</b>
		3/4	44.5 (1.75)	<b>GSK-75-20</b>
	Blank Cover	Blank	26.9 (1.06)	<b>GSK-BC-20</b>
	<b>GS — Cover, Lamp Receptacle — Furnished with gasket and screws</b>	—	41.4 (1.63)	<b>GSK-LR20</b>
	<b>GS-20 — Connection Block — Furnished with mounting screws. 5-Wire, 20 A, 300 Volt</b>	—	—	<b>CB205</b>