

# ATX™ JBES and ECES Series 316L Stainless Steel Enclosure Accessories

Increased Safety

ATEX/IECEX:  
Zone 1 and 2 - 21 and 22  
II 2 GD  
IP66 - IK10

## Mounting Accessories - Continued

	Dimensions mm (in)			Gland Plate/Coupling Flange Dimensions mm (in)	Catalog Number
	Enclosure Width	Height			
<b>Spare Gland Plate</b>					
	220 (8.66)	150 (5.91)	B/D	170 x 120 (6.69 x 4.72)	JBESGP221B
	260 (10.24)	150 (5.91)	A/C	250 x 120 (9.84 x 4.72)	JBESGP261A
	260 (10.24)	200 (7.87)	A/C	250 x 170 (9.84 x 6.69)	JBESGP262A
	260 (10.24)	200 (7.87)	B/D	210 x 170 (8.27 x 6.69)	JBESGP262B
	370 (14.57)	200 (7.87)	A/C	360 x 170 (14.17 x 6.69)	JBESGP372A
	370 (14.57)	200 (7.87)	B/D	320 x 170 (12.60 x 6.69)	JBESGP372B
	560 (22.05)	200 (7.87)	A/C	550 x 170 (21.65 x 6.69)	JBESGP562A
	560 (22.05)	200 (7.87)	B/D	510 x 170 (20.08 x 6.69)	JBESGP562B
	750 (29.53)	200 (7.87)	A/C	740 x 170 (29.13 x 6.69)	JBESGP752A
	750 (29.53)	200 (7.87)	B/D	700 x 170 (27.56 x 6.69)	JBESGP752B
	260 (10.24)	300 (11.81)	A/C	250 x 270 (9.84 x 10.63)	JBESGP263A
	370 (14.57)	300 (11.81)	A/C	360 x 270 (14.17 x 10.63)	JBESGP373A
	370 (14.57)	300 (11.81)	B/D	320 x 270 (12.60 x 10.63)	JBESGP373B
	560 (22.05)	300 (11.81)	A/C	550 x 270 (21.65 x 10.63)	JBESGP563A
	560 (22.05)	300 (11.81)	B/D	510 x 270 (20.08 x 10.63)	JBESGP563B
	750 (29.53)	300 (11.81)	A/C	740 x 270 (29.13 x 10.63)	JBESGP753A
750 (29.53)	300 (11.81)	B/D	700 x 270 (27.56 x 10.63)	JBESGP753B	
<b>Coupling Flange</b>					
	260 (10.24)	200 (7.87)	A/C	250 x 120 (9.84 x 4.72)	JBESCF262A
	370 (14.57)	200 (7.87)	A/C	360 x 170 (14.17 x 6.69)	JBESCF372A
	370 (14.57)	200 (7.87)	B/D	320 x 170 (12.60 x 6.69)	JBESCF372B
	560 (22.05)	200 (7.87)	A/C	550 x 170 (21.65 x 6.69)	JBESCF562A
	560 (22.05)	200 (7.87)	B/D	510 x 170 (20.08 x 6.69)	JBESCF562B
	750 (29.53)	200 (7.87)	A/C	740 x 170 (29.13 x 6.69)	JBESCF752A
	750 (29.53)	200 (7.87)	B/D	700 x 170 (27.56 x 6.69)	JBESCF752B
	370 (14.57)	300 (11.81)	A/C	360 x 270 (14.17 x 10.63)	JBESCF373A
	370 (14.57)	300 (11.81)	B/D	320 x 270 (12.60 x 10.63)	JBESCF373B
	560 (22.05)	300 (11.81)	A/C	550 x 270 (21.65 x 10.63)	JBESCF563A
	560 (22.05)	300 (11.81)	B/D	510 x 270 (20.08 x 10.63)	JBESCF563B
	750 (29.53)	300 (11.81)	A/C	740 x 270 (29.13 x 10.63)	JBESCF753A
	750 (29.53)	300 (11.81)	B/D	700 x 270 (27.56 x 10.63)	JBESCF753B

 **Appleton**

ENCLOSURES AND JUNCTION BOXES: ATEX/IECEX INCREASED SAFETY JUNCTION BOXES