

# JB Conduit Outlet Boxes, Covers and Hangers

UNILETS™ for use with Threaded Rigid Metal Conduit and IMC. Furnished with Internal Ground Screw.

NEC:  
Listed for Ordinary Locations

COMMERCIAL AND INDUSTRIAL FITTINGS: CONDUIT OUTLET BODIES

## Applications

- Serve as pulling fittings.
- Provide openings for splicing.
- Make straight connections and 90° bends in conduit runs.
- Permit access to conductors for maintenance.

## Features

- Raintight when enclosed and gasketed with hub or blank covers.
- Furnished with internal ground screw.
- Blind cover screw holes prevent conductor damage during installation, provide water-tightness.
- Available in three inside depths: 1-5/16", 2-1/16", and 3-1/8".
- Order with or without mounting lugs.
- Furnished with four tapped holes and two close-up plugs.
- Cushion fixture hangers are enclosed and gasketed.

## Standard Materials

- JB conduit outlet boxes and covers and JB fixture hangers: malleable iron
- JB-A boxes and covers: copperfree (4/10 of 1% max.) aluminum
- Gaskets: neoprene

## Standard Finishes

- Malleable iron conduit outlet boxes, and hub covers: triple-coat – (1) zinc electroplate, (2) chromate and (3) epoxy powder coat
- Fixture hangers, JB 1/2" hub and blank covers: triple-coat – (1) zinc electroplate, (2) chromate and (3) epoxy powder coat
- Aluminum JB conduit outlet boxes: epoxy powder coat

## NEC Certifications and Compliances

- UL Standard: 514A
- UL Listed: E2527
- NEMA Standard: FB-1

	Description	Hub Size (Inches)	Catalog Number	
			Malleable Iron	Aluminum
<b>JBX – 1-5/16" Inside Depth – Furnished with four tapped openings and two close-up plugs</b>				
	Less mounting lugs	1/2	<b>JBX-50</b>	—
		3/4	<b>JBX-75</b>	—
		1	<b>JBX-100</b>	—
	With mounting lugs	1/2	<b>JBX-50L</b>	<b>JBX50L-A</b>
		3/4	<b>JBX-75L</b>	<b>JBX75L-A</b>
		1	<b>JBX-100L</b>	—
<b>JBDX – 2-1/16" Inside Depth – Furnished with four tapped openings and two close-up plugs</b>				
	Less mounting lugs	1/2	<b>JBDX-50</b>	—
		3/4	<b>JBDX-75</b>	—
		1	<b>JBDX-100</b>	—
	With mounting lugs	1/2	<b>JBDX-50L</b>	—
		3/4	<b>JBDX-75L</b>	—
		1	<b>JBDX-100L</b>	—
<b>JBLX – 3-1/8" Inside Depth – Furnished with four tapped openings and two close-up plugs</b>				
	With removable mounting lugs	1/2	<b>JBLX-50L</b>	<b>JBLX-50L-A</b>
		3/4	<b>JBLX-75L</b>	<b>JBLX-75L-A</b>
		1	<b>JBLX-100L</b>	<b>JBLX-100L-A</b>