

# Mercmaster™ LED Series Luminaires

## Enclosed and Gasketed Fixtures

**NEC/CEC:**

Class I, Division 2, Groups A, B, C, D  
 Class I, Zone 2, AEx nA IIC  
 Class II, Division 1, Group E, F, G  
 Class II, Division 2, Group F, G  
 Class III

**NEC/CEC:**

Type 3R, 4, 4X  
 IP66/67  
 Simultaneous Exposure  
 Suitable for Use in Wet Locations  
 Marine Outside Type (Salt Water)

**ATEX/IECEX:**

Zone 2 and 22  
 II 2 GD  
 IP66/67

### Mounting Hoods ①

	Description	Hub Size	Catalog Number NEC/CEC and ATEX/IEC
<b>Pendant</b>			
	One Hub, Rigid Mounting	3/4 1 M20	KPA-75 KPA-100 KPA-M20
<b>Pendant Cone</b>			
	One Hub, Rigid Mounting	3/4 1 M20	KPCH-75 KPCH-100 KPCH-M20
<b>Ceiling</b>			
	Five Hubs, Four Close-Up Plugs	3/4 1 M20	KPC-75 KPC-100 KPC-M20
<b>Wall</b>			
	Five Hubs, Four Close-Up Plugs	3/4 1 M20	KPWB-75 KPWB-100 KPWB-M20
<b>25° Stanchion</b>			
	One Hub	1-1/4 1-1/2	KPS-125 KPS-150
<b>90° Stanchion</b>			
	One Hub	1-1/4 1-1/2	KPST-125 KPST-150

### Mercmaster LED Ballast and Mounting Hood Weights

Description	Weight kg (lb)
Fixture Unit (Ballast Housing)	8.8 (19.4)
Pendant Mounting Hood	1.0 (2.25)
Pendant Cone Mounting Hood	1.1 (2.50)
Ceiling Mounting Hood	1.4 (3.00)
Wall Mounting Hood	1.8 (4.00)
25° Stanchion Mounting Hood	1.5 (3.25)
90° Stanchion Mounting Hood	1.7 (3.75)

① For ATEX/IECEX rated fixtures, ballast bodies and mounting hoods must be purchased separately.