

# Mercmaster™ LED Series Luminaires

## Enclosed and Gasketed Fixtures

NEC/CEC: Class I, Division 2, Groups A, B, C, D | Class I, Zone 2, AEx nA IIC | Class II, Division 1, Group E, F, G | Class II, Division 2, Group F, G | Class III | Type 3R, 4, 4X | IP66/67 | Simultaneous Exposure | Suitable for Use in Wet Locations | Marine Outside Type (Salt Water)

### Fixture Unit — Driver Housing

	Lumen Level	LED Wattage	Light Level Equivalent	NEMA Type	Voltage	Catalog Number	Fuse Kit Suffix
	5650	61/64 W	150 W HPS	Type V	120-277 Vac, 50/60 Hz	MLEDN15P5BU	F3
	5650	74/88 W	175 W PSMH	Type V	120-277 Vac, 50/60 Hz	MLEDN17P5BU	F3
	5650	70/69 W	175 W PSMH	Type I	120-277 Vac, 50/60 Hz	MLEDN17P1BU	F3
	5650	92/96 W	250 W HPS/PSMH	Type V	120-277 Vac, 50/60 Hz	MLEDN25P5BU	F3
	5650	102/103 W	350 W PSMH	Type V	347-480 Vac, 50/60 Hz	MLEDN35P5BH	F3
	5650	127/128 W	400 W HPS/PSMH	Type V	120-277 Vac, 50/60 Hz	MLEDN40P5BU	F3

### Mounting Hoods

	Description	Hub Size	Catalog Number
<b>Pendant</b>		3/4	KPA-75
		1	KPA-100
<b>Pendant Cone</b>		3/4	KPCH-75
		1	KPCH-100
<b>Ceiling</b>		3/4	KPC-75
		1	KPC-100
<b>Wall</b>		3/4	KPWB-75
		1	KPWB-100
<b>25° Stanchion</b>		1-1/4	KPS-125
		1-1/2	KPS-150
<b>90° Stanchion</b>		1-1/4	KPST-125
		1-1/2	KPST-150

LED Luminaires | NEC/CEC Certified | Hazardous Location