

# EFD/EFDB Series Factory Sealed Control Stations

## Explosionproof, Dust-Ignitionproof

### NEC:

Class I, Division 1 and 2, Groups B+, C, D  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III  
 NEMA 3, 7CD, 9EFG

### Nameplates ①

Description	Suffix
<b>Mushroom Head Push Buttons (Maintained and Momentary)</b>	
Start	MNPSTQ
Stop	MNPSPQ
Emergency Stop	MNPESTPQ
Blank	MNPBQ
<b>Pilot Light Nameplates</b>	
Blank	LNPBQ
Forward	LNPFWQ
Jog	LNPJOGQ
Run	LNPRUNQ
Stop	LNPSPQ
Start	LNPSTQ
Down	LNPDOWNQ
Fast	LNPFASTQ
Slow	LNPSLOWQ
Raise	LNPRAISEQ
Lower	LNPLOWERQ
Reset	LNPRESETQ
Off	LNPOFFQ
On	LNPONQ
Reverse	LNPREVQ
Close	LNPCLOSEQ
Open	LNPOPENQ
Up	LNPUPQ
Test	LNPTTESTQ
Low	LNPLOWQ
High	LNPHIGHQ
<b>Two Position Selection Switch Nameplates</b>	
Forward—Reverse	SLNPFRQ
Hand—Auto ②	SLNPHAQ
On—Off	SLNPOO
Start—Stop	SLNPSS
Blank	SLNPBQ
Up—Down	SLNPUDQ
Run—Jog	SLNPRJQ
Auto—Hand	SLNPAHQ
Off—Remote	SLNPORQ

Description	Suffix
<b>Three Position Selection Switch Nameplates</b>	
Forward—Off—Reverse	SLNPFORQ
Hand—Off—Auto ②	SLNPHOAQ
Run—Off—Jog	SLNPROJQ
Blank	SLNPB3
Reverse—Off—Forward	SLNPROFQ
Auto—Off—Hand	SLNPAOHQ
Hand—Off—Remote	SLNPHORQ
1—Off—2	SLNP102Q
Jog—Off—Run	SLNPJORQ
Stop—Run—Start	SLNPSRSQ
Local—Off—Remote	SLNPLOQ
<b>Momentary Push Buttons</b>	
<i>For Rectangular Weatherboot Style Only (Not for round weatherboot style)</i>	
Blank ②	SNPBQ
Forward	SNPFWQ
Jog	SNPJOGQ
Run	SNPRUNQ
Stop ②	SNPSPQ
Start ②	SNPSTQ
Down	SNPDOWNQ
Fast	SNPFASTQ
Slow	SNPSLOWQ
Raise	SNPRAISEQ
Lower	SNPLOWERQ
Reset	SNPRESETQ
Off	SNPOFFQ
On	SNPONQ
Reverse	SNPREVQ
Close	SNPCLOSEQ
Open	SNPOPENQ
Up	SNPUPQ
Test	SNPTTESTQ
Low	SNPLOWQ
High	SNPHIGHQ

① Custom nameplates are not available.

② Included as standard (no need to use suffix).


◆ Select items suitable for Class I, Division 1 and 2, Groups B, C and D; Class II, Groups E, F and G and Class III. See product selection pages for suitable items.

# EFD/EFDB and EDS Series Factory Sealed Control Stations

## EFD/EFDB Push Button Accessories and Parts

**NEC:**

Class I, Division 1 and 2, Groups B, C, D  
 Class II, Division 1 and 2, Groups E, F, G  
 Class III

		Description		Catalog Number	
<b>Nameplates for Rectangular Push Buttons</b>					
 <b>SNP-OFF-Q</b>		Blank	<b>SNP-B-Q</b>	Off	<b>SNP-OFF-Q</b>
		Forward	<b>SNP-FWD-Q</b>	On	<b>SNP-ON-Q</b>
		Jog	<b>SNP-JOG-Q</b>	Reverse	<b>SNP-REV-Q</b>
		Run	<b>SNP-RUN-Q</b>	Open	<b>SNP-OPEN-Q</b>
		Stop	<b>SNP-SP-Q</b>	Close	<b>SNP-CLOSE-Q</b>
 <b>SNP-ON-Q</b>		Start	<b>SNP-ST-Q</b>	Up	<b>SNP-UP-Q</b>
		Down	<b>SNP-DOWN-Q</b>	Test	<b>SNP-TEST-Q</b>
		Fast	<b>SNP-FAST-Q</b>	Low	<b>SNP-LOW-Q</b>
		Slow	<b>SNP-SLOW-Q</b>	High	<b>SNP-HIGH-Q</b>
		Raise	<b>SNP-RAISE-Q</b>		
		Lower	<b>SNP-LOWER-Q</b>		
		Reset	<b>SNP-RESET-Q</b>		
<b>Push Button Replacement Locking Guards — Glass Reinforced Polypropylene — Gasketed</b>					
 <b>Maintained Switch Guard</b>   <b>Single Guard</b>   <b>Double Guard</b>		<i>Has hole for 1/4" hasp.</i>			
		Single Guard (Maintained Switch)		<b>SMPB-LG</b>	
		Single Guard		<b>NPB-LG1</b>	
		Double Guard		<b>NPB-LG2</b>	
		Single Guard (No Lockout Holes)		<b>NPB-LG1-LL</b>	
	Double Guard (No Lockout Holes)		<b>NPB-LG2-LL</b>		
<b>Push Button Securing Rod with Chain — Stainless Steel</b>					
		For use with Single Guard Only		<b>NBL-SR</b>	
<b>Mushroom Button with Weather Boot for Use with Momentary Contact — Gasketed</b>					
		Black		<b>NMRB-BL</b>	
		Green		<b>NMRB-GR</b>	
		Red		<b>NMRB-RE</b>	
<b>Mushroom Button</b>					
		<b>For Use with Maintained Contact — Solid-Colored Nonmetallic Button</b>			
		Red		<b>NMRBM-RE</b>	
<b>Nameplates For Momentary and Maintained Mushroom Head Push Button</b>					
 <b>MNPESTPQ</b>		Start		<b>MNPSTQ</b>	
		Stop		<b>MNPSPQ</b>	
		Emergency Stop		<b>MNPESTPQ</b>	
		Blank		<b>MNPBQ</b>	