

EFD/EFDB and EDS Series Factory Sealed Control Stations

ESK/EFK Covers For Pilot Lights, Push Buttons, or Selector Switches.

NEC:

Class I, Division 1 and 2, Groups C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III

Covers Only — for use on standard EFD bodies

Supplied with 4 cover bolts and blank cover nameplate.

		Description	Catalog Number
Push Button or Pilot Light Covers — 3/4" Tapped Openings ①			
		One opening: one push button or one pilot light	ESKB-1PBQ
ESKB-1PBQ	ESKB-2PBQ	Two openings: two push buttons, two pilot lights, or one of each	ESKB-2PBQ
		Three openings: three device (EFDL) three push buttons or three pilot lights, or combination of push button(s) and pilot light(s)	EFKL-3HQ ②
EFKL-3HQ			
Push Button or Selector Switch Cover — 1/2" Tapped Openings ①			
		Two openings: selector switch or two push buttons	ESKB-2SPQ
Push Button, Pilot Light or Selector Switch Covers — 3/4" top and 1/2" Bottom Tapped Openings ①			
		One top and two bottom openings: one pilot light, two push buttons; one pilot light, one selector switch.	ESKB-3JPBQ
ESKB-3JPBQ	ESKB-BQ	Blank	ESKB-BQ
Nameplate Mounting Bracket			
		Bracket with blank silver/black nameplate for EFDB series	NPBRKT-EFDB
		Bracket with blank silver/black nameplate for 3-device EFD series	NPBRKT-CONT
		To order bracket with control station, add suffix -NPBRKT to end of catalog number.	
		To order engraved nameplates, add desired markings after catalog number. Maximum of 2 lines with 12 characters (including spaces) per line.	
		<i>Note: Mount bracket between cover screws and cover. Do not mount bracket between ground joint flame path between cover and backbox.</i>	

① All covers are copperfree aluminum. Supplied with four captive stainless steel bolts.

② Catalog number EFKL-3HQ supplied with 6 stainless steel non-captive bolts.

EDS Factory Sealed Tumbler Switches

Explosionproof, Dust-Ignitionproof

Malleable Iron Body and Cover. Furnished with Internal Ground Screw.

NEC:

Class I, Division 1 and 2, Groups C, D
 Class II, Division 1 and 2, Groups E, F, G
 Class III
 NEMA 3, 7CD, 9EFG

Factory Assembled Switch Assembly

	Switch Type	Catalog Number			
		20 Amp, 120–277 Vac ①		30 Amp, 120–277 Vac ②	
		Malleable Iron	Aluminum	Malleable Iron	Aluminum
 <p>Front Cover</p>	1-Pole	EDKF21-Q ③	EDKF21-AQ ③	EDKF31-Q ④	EDKF31-AQ ④
	2-Pole	EDKF22-Q ③	EDKF22-AQ ③	EDKF32-Q ④	EDKF32-AQ ④
	3-Way	EDKF23W-Q ③	EDKF23W-AQ ③	EDKF33W-Q ④	EDKF33W-AQ ④
	4-Way	EDKF24W-Q ④	EDKF24W-AQ ④	—	—
 <p>Rocker Cover/Chamber</p>	1-Pole	EDK-R21-Q ③		EDK-R31-Q ④	
	2-Pole	EDK-R22-Q ③		EDK-R32-Q ④	
	3-Way	EDK-R23W-Q ③		EDK-R33W-Q ④	
	4-Way	EDK-R24W-Q ④		—	
 <p>Factory Sealed Switch Only</p>	1-Pole	LAB21		—	
	2-Pole	LAB22		—	
	3-Way	LAB23W		—	

Nameplate Mounting Bracket

Description	Catalog Number
 <p>Bracket with blank silver/black nameplate for EFDB series</p> <p>To order bracket with control station, add suffix -NPBRKT to end of catalog number.</p> <p>To order engraved nameplates, add desired markings after catalog number. Maximum of 2 lines with 12 characters (including spaces) per line.</p> <p><i>Note: Mount bracket between cover screws and cover. Do not mount bracket between ground joint flame path between cover and backbox.</i></p>	NPBRKT-EFDB

① 20 Amp Switches 1 HP at 120 Vac and 2 HP at 240 Vac.
 ② 30 Amp Switches 2 HP at 120 Vac or 240 Vac.
 ③ Contains Factory Sealed Switch; no sealing chamber.
 ④ With sealing chamber.