

Intraground™ N1 and N2 Series Control Station


Nonmetallic

10 Ampere, 600 Vac Max. for Heavy Duty Use. N1 Series – Neutral Color; N2 Series – Blue Color.

NEC:

Class I, Division 1 and 2, Groups B*, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III

Push Button Accessories and Parts

	Description	Catalog Number
	Push Button Securing Rod with Chain – Stainless Steel For use with Single Guard Only	NBL-SR
	Mushroom Head Button with Weather Boot for Use with Momentary Contact – Gasketed Black Green Red	NMRB-BL NMRB-GR NMRB-RE
	Mushroom Head Push Button For Use with Mushroom Head Push Button – Maintained Contact – Solid-Colored Nonmetallic Red	NMRBM-RE
	Nameplates – Mushroom Head Push Button For Momentary and Maintained Start Stop Emergency Stop Blank	MNPSTQ MNPSPQ MNPESTPQ MNPBQ
	Pilot Light, Factory Sealed Incandescent Furnished with 6S6 120 Vac incandescent lamp, jewel and guard. Has 457 mm (18") long, type SFF-2 pigtail leads; +150 °C (+302 °F). Body has 3/4" straight thread (NPSM). With Red Jewel With Green Jewel With Amber Jewel With Blue Jewel With Clear Jewel With Opal Jewel	SPLSREB SPLSGRB SPLSAMB SPLSBLB SPLSCLB SPLSOPB
	Chamber Only LED Furnished with candelabra base 120 Vac LED, jewel and guard. Has 457 mm (18") long, type SFF-2 pigtail leads; +150 °C (+302 °F). Body has 3/4" straight thread (NPSM). With Red LED, Clear Jewel With Green LED, Clear Jewel With Amber LED, Clear Jewel	SPLNSREB SPLNSGRB SPLNSAMB
	Chamber Only (Same as above, less jewel, guard and lamp)	SPLSSCB

♦ Suitable for Class I, Group B when installed in an enclosure rated for Class I, Group B.