

# U-Line™ Factory Sealed 20 Amp Malleable Iron Receptacles

## Explosionproof, Dust-Ignitionproof

125 Vac, 20 Amp, 1 HP; 250 Vac, 20 Amp, 2 HP. Dead-Front Safety Construction.

### NEC/CEC ①:

Class I, Division 1, Groups B<sup>+</sup>, C, D  
 Class I, Division 2, Groups B, C, D  
 Class II, Division 1 and 2, Groups F, G  
 Class III  
 NEMA 3, 3R, 3RX, 7BCD, 9FG

### Malleable Iron Receptacle Cover and Malleable Iron Mounting Box

	Type	Wire/Pole	Hub Size (Inches)	Catalog Number	
				125 Vac, 1 HP 	250 Vac, 2 HP 
<b>Two Gang</b>					
<i>Class I, Division 1 and 2 Groups C, D; Class I, Division 2, Groups B, C, D; Class II, Division 1 and 2 Groups F, G; Class III.</i>					
	Dead-End	2W, 3P	1/2	EFS250-2023M	EFS250-20232M
			3/4	EFS275-2023M	EFS275-20232M
			1	EFS210-2023M	EFS210-20232M
	Feed-Thru	2W, 3P	1/2	EFSC250-2023M	EFSC250-20232M
			3/4	EFSC275-2023M	EFSC275-20232M
			1	EFSC210-2023M	EFSC210-20232M
Dead-End	Feed-Thru				

### Malleable Iron Replacement Receptacle



20A Receptacle Cover 2W, 3P (iron)	EFSR-2023M	EFSR-20232M
Spring-loaded Cover Replacement Assembly (iron)	ULSCM	

APPLETON™

PLUGS AND RECEPTACLES: NEC/CEC HAZARDOUS LOCATION

① For CEC version with CSA nameplate, add suffix **-CN** to catalog number.

◆ Select items suitable for Class I, Group B, C and D; Class II, Groups F, G; and Class III. See product selection pages for suitable items.