

V-51™ Incandescent Luminaires

Enclosed and Gasketed

UNILETS® for use with threaded metal conduit. Fixtures suitable for use in wet locations. ①

NEC:
Class I, Division 2, Groups A, B, C, D

CEC:
Class I, Division 2, Groups A, B, C, D
Class II, Divisions 1 and 2, Groups E, F, G ②
Class III
Enclosure 3R

Appleton

INCANDESCENT/AREA: NEC/CEC ENCLOSED AND GASKETED

| Malleable Mounting Hood, Adapter and Guard | Type | Lamp Watts | Size (Inches) | All Malleable with Guard ③ |
|---|-------|------------|---------------|----------------------------|
| Pendant | | | | |
|  | A-21 | 60-150 | 1/2 | VA1050G-M |
| | | | 3/4 | VA1075G-M |
| | | | 1 | VA1100G-M |
| | | | 1-1/4 | VA1125G-M |
| | PS-30 | 150-300 | 1/2 | VA2050G-M |
| | | | 3/4 | VA2075G-M |
| | | | 1 | VA2100G-M |
| | | | 1-1/4 | VA2125G-M |
| Ceiling — Five Tapped Openings — Four close-up plugs | | | | |
|  | A-21 | 60-150 | 1/2 | VXHA1050G-M |
| | | | 3/4 | VXHA1075G-M |
| | | | 1 | VXHA1100G-M |
| | | | 1/2 | VXHA2050G-M |
| | PS-30 | 150-300 | 3/4 | VXHA2075G-M |
| | | | 1 | VXHA2100G-M |
| Wall — JB Box Mounting ④ — Fits JB cast outlet box ⑤ — Screws and gasket furnished with fixture | | | | |
|  | A-21 | 60-150 | | JBW10G-M |
| | PS-30 | 150-300 | | JBW20G-M |
| Ceiling — JB Box Mounting ④ — Fits JB cast outlet box ⑤ — Screws and gasket furnished with fixture | | | | |
|  | A-21 | 60-150 | | JB10G-M |
| | PS-30 | 150-300 | | JB20G-M |

① With heat-resistant glass globes or plastic globes.

② 300 W PS-25 not approved for Class II, Division 1 and 2, Group G; Class III.

③ To order fixtures without guards, omit -G suffix from catalog number. Order reflectors and accessories separately.

④ 30° angle reflector adaptable for 100 W fixture only, when mounted at least 114.3 mm (4.5") from wall.

⑤ JB cast outlet box is available in the Fitting Section.