

V-51™ Incandescent Luminaires

Enclosed and Gasketed

UNILETS® for use with threaded metal conduit.

NEC:
Class I, Division 2, Groups A, B, C, D

CEC:
Class I, Division 2, Groups A, B, C, D
Class II, Divisions 1 and 2, Groups E, F, G ②
Class III
Enclosure 3R

Description	Hub Size (Inches)	Catalog Numbers Malleable Iron
Pendant and Ceiling Mounting Hoods — Furnished with connection block, gasket and screws		
Pendant Mounting		
	1/2	VA50
	3/4	VA75
	1	VA100
	1-1/4	VA125
Dead-End — Ceiling Mounting		
	1/2	V50
	3/4	V75
Feed-Thru — Ceiling Mounting		
	1/2	VC50
	3/4	VC75
Three Hubs — Ceiling Mounting		
	1/2	VT50
	3/4	VT75
Four Hubs — Ceiling Mounting		
	1/2	VX50
	3/4	VX75
Five Hubs — Ceiling Mounting ③		
	1/2	VXHA50
	3/4	VXHA75
	1	VXHA100
Wall and Stanchion Mounting Hoods — Furnished with connection block, gasket and screws		
One Opening — Wall Mounting ④ — 1 tapped hole in center of flange		
	1/2	VGA50
	3/4	VGA75
Feed-Thru — Wall Mounting ④ — 2 tapped vertical feed-thru hubs		
	1/2	VD50
	3/4	VD75
Three Hubs and One Opening — Wall Mounting ④ — 3 hubs plus 1 tapped opening in center of flange		
	1/2	VGAT50
	3/4	VGAT75

② 300 W PS-25 not approved for Class II, Division 1 and 2, Group G; Class III.

③ Four close-up plugs furnished.

④ Mounting hoods for wall installations can only be used with 30° angle reflectors.