

# Stylmaster™ Incandescent Luminaires

## Enclosed and Gasketed

Attractively styled fixture with prismatic globe. UNILETS® for use with threaded metal conduit.

**NEC:**  
Class I, Division 2, Groups A, B, C, D

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
Enclosure 4X

	Description	Hub Size (Inches)	Catalog Numbers	
			NEC	CEC
<b>Pendant</b>				
	Furnished with setscrew, 3/4" to 1/2" reducer for 1/2" stem, medium base socket.		<b>VPA75</b>	<b>VCA75</b>
<b>Ceiling – Five Tapped Openings</b>				
	Four close-up plugs	1/2	<b>VPX50</b>	<b>VCX50</b>
		3/4		<b>VCX75</b>
<b>45° Stanchion</b>				
		1-1/4	<b>VPAN125</b>	<b>VCAN125</b>
<b>Wall – Five Tapped Openings in Outlet Box ①</b>				
	Four close-up plugs	1/2	<b>VPWB50</b>	—
		3/4	<b>VPWB75</b>	—
<b>Cast Outlet Box Only – Five Tapped Openings</b>				
	Four close-up plugs. No socket. Fits VPOB, VPOBW and VPWB.	1/2	<b>VPJB50</b>	<b>VCJB50</b>
		3/4	<b>VPJB75</b>	<b>VCJB75</b>
<b>Ceiling – For Outlet Box</b>				
	(Octagonal outlet boxes for non-classified areas only) Fits SEH or VPJB cast outlet box, or 4" octagonal outlet box. With screws and gasket.		<b>VPOB1</b>	<b>VCOB1</b>
<b>Wall – For Outlet Box ①</b>				
	(Octagonal outlet boxes for non-classified areas only) Fits SEH or VPJB cast outlet box, or 4" octagonal outlet box. With screws and gasket.		<b>VPOBW1</b>	<b>VCOBW1</b>
<b>Wall – Outlet Box Mounting with Side Hubs – With two side hubs and one close-up plug</b>				
	(Octagonal outlet boxes for non-classified areas only)	3/4	—	<b>VCB75</b>

① Use 30° angle reflectors for wall installations – center line of fixture must be located at least 5-3/4" away from wall. Has four 3/16" dia. mounting holes located 90° apart on a 3-1/2" dia. center.

# Stylmaster™ Incandescent Luminaires

## Enclosed and Gasketed

Attractively styled fixture with prismatic globe. UNILETS® for use with threaded metal conduit.

**NEC:**  
Class I, Division 2, Groups A, B, C, D

**CEC:**  
Class I, Division 2, Groups A, B, C, D  
Class II, Division 1 and 2, Groups E, F, G  
Class III  
Enclosure 4X

	Description	Catalog Number	
		Porcelain Steel	Polyester
	Standard Dome Reflector	LPR-25ST	LPRP-25ST
	30° Angle Reflector	LPR-25AN	LPRP-25AN

### Weights

Typical Mounting Hoods							
Pendant	kg (lb)	Ceiling	kg (lb)	Wall	kg (lb)	Stanchion	kg (lb)
VPA75	0.9 (1.98)	VPX75	0.9 (1.98)	VPOBW10	1.4 (3.09)	VPAN-125	1.4 (3.09)
VCA75		VCX75		VCOBW10		VCAN-125	

Globes and Guards					Reflectors			
Type	Globe	kg (lb)	Guard	kg (lb)	Standard Dome	kg (lb)	30° Angle	kg (lb)
60-200 W	VPGL-1	0.9 (1.98)	VPGU-1	0.5 (1.10)	LPR-25ST	1.4 (3.09)	LPR-25AN	0.9 (1.98)
200-300 W	VPGL-2	1.4 (3.09)	VPGU-2	0.5 (1.10)	LPRP-25ST	0.9 (1.98)	LPRP-25AN	0.9 (1.98)