

Stylmaster™ Incandescent Luminaires

Enclosed and Gasketed

Attractively styled fixture with prismatic globe. UNILETS® for use with threaded metal conduit.

NEC:
Class I, Division 2, Groups A, B, C, D

CEC:
Class I, Division 2, Groups A, B, C, D
Class II, Division 1 and 2, Groups E, F, G
Class III
Enclosure 4X

Description	Hub Size (Inches)	Catalog Numbers	
		NEC	CEC
Pendant			
 Furnished with setscrew, 3/4" to 1/2" reducer for 1/2" stem, medium base socket.		VPA75	VCA75
Ceiling – Five Tapped Openings			
 Four close-up plugs	1/2	VPX50	VCX50
	3/4		VCX75
45° Stanchion			
	1-1/4	VPAN125	VCAN125
Wall – Five Tapped Openings in Outlet Box ①			
 Four close-up plugs	1/2	VPWB50	—
	3/4	VPWB75	—
Cast Outlet Box Only – Five Tapped Openings			
 Four close-up plugs. No socket. Fits VPOB, VPOBW and VPWB.	1/2	VPJB50	VCJB50
	3/4	VPJB75	VCJB75
Ceiling – For Outlet Box			
 (Octagonal outlet boxes for non-classified areas only)			
Fits SEH or VPJB cast outlet box, or 4" octagonal outlet box. With screws and gasket.		VPOB1	VCOB1
Wall – For Outlet Box ①			
 (Octagonal outlet boxes for non-classified areas only)			
Fits SEH or VPJB cast outlet box, or 4" octagonal outlet box. With screws and gasket.		VPOBW1	VCOBW1
Wall – Outlet Box Mounting with Side Hubs — With two side hubs and one close-up plug			
 (Octagonal outlet boxes for non-classified areas only)	3/4	—	VCB75

① Use 30° angle reflectors for wall installations – center line of fixture must be located at least 5-3/4" away from wall. Has four 3/16" dia. mounting holes located 90° apart on a 3-1/2" dia. center.