



Cable Types and Ranges

Style	Part Number (ST = Snap-Tite®)	Knock-Out Size	ACG90	AC90	TECK90	Outer Armor Diameter Flex • A/C • M/C	Throat Diameter	Number of Cables	Insulated Throat	Flexible Metal Conduit (FMC)				Armored Cable (A/C)		Metal Clad Cable (M/C)		A/C M/C	
										Steel	Aluminum	Reduced Wall Steel	Reduced Wall Aluminum	Steel	Aluminum	Steel	Aluminum Corrugated		Aluminum Continuous Corrugated
90° Two Screw Clamp Type Connectors	85	1/2				0.370 - 0.510	0.620	1											
	85A	1/2				0.370 - 0.510	0.620	1											
	85ST	1/2				0.370 - 0.510	0.560	1											
	85AST	1/2				0.370 - 0.510	0.560	1											
	850	1/2		0.480 - 0.650		0.440 - 0.750	0.620	1											
	850A	1/2		0.480 - 0.650		0.440 - 0.750	0.560	1											
	850ST	1/2		0.480 - 0.650		0.440 - 0.750	0.620	1											
	850AST	1/2		0.480 - 0.650		0.440 - 0.750	0.560	1											
	851	1/2		0.650 - 0.850		0.635 - 1.085	0.620	1											
	851A	1/2		0.650 - 0.850		0.635 - 1.085	0.560	1											
	851ST	1/2		0.650 - 0.850		0.635 - 1.085	0.620	1											
	851AST	1/2		0.650 - 0.850		0.635 - 1.085	0.560	1											
	852	3/4				0.830 - 1.380	0.825	1											
	852A	3/4				0.830 - 1.380	0.765	1											
	853	1				1.330 - 1.570	1.025	1											
	853A	1				1.330 - 1.570	0.974	1											
	854	1-1/4				1.625 - 1.940	1.375	1											
	854A	1-1/4				1.625 - 1.940	1.294	1											
	855	1-1/2				1.400 - 2.400	1.575	1											
	855A	1-1/2				1.400 - 2.400	1.532	1											
	856	2				1.400 - 2.400	2.030	1											
	856A	2				1.400 - 2.400	2.007	1											
	857	2-1/2				2.600 - 3.100	2.450	1											
	857A	2-1/2				2.600 - 3.100	2.425	1											
	858	3				3.100 - 3.640	3.140	1											
858A	3				3.100 - 3.640	3.050	1												
859	3-1/2				3.380 - 4.220	3.540	1												
859A	3-1/2				3.380 - 4.220	3.960	1												
8510	4				3.730 - 3.730	3.540	1												
8510A	4				3.730 - 3.730	3.960	1												
Squeeze Connectors	L42	1/2				0.530 - 0.620	0.400	1											
	L420	1/2				0.530 - 0.620	0.400 x 0.580	1											
	L421	1/2				0.850 - 0.910	0.620	1											
	L421A	1/2				0.850 - 0.910	0.620	1											
	L422	3/4				1.100 - 1.135	0.820	1											
	L422A	3/4				1.100 - 1.135	0.820	1											
	L423	1				1.255 - 1.375	0.940	1											
	L423A	1				1.255 - 1.375	0.940	1											
	L424	1-1/4				1.550 - 1.610	1.240	1											
	L424A	1-1/4				1.550 - 1.610	1.240	1											
	L425	1-1/2				1.810 - 1.895	1.460	1											
	L425A	1-1/2				1.810 - 1.895	1.460	1											
	L426	2				2.260 - 2.485	1.935	1											
	L426A	2				2.260 - 2.485	1.935	1											
	L427	2-1/2				2.770 - 2.950	2.440	1											
	L427A	2-1/2				2.770 - 2.950	2.440	1											
	L428	3				3.170 - 3.560	2.980	1											
L428A	3				3.170 - 3.560	2.980	1												
L429	3-1/2				3.630 - 4.155	3.478	11												
L429A	3-1/2				3.630 - 4.155	3.478	1												
L4210	4				4.030 - 4.635	3.977	1												
L4210A	4				4.030 - 4.635	3.977	1												

Flex • AC • MC