

Associated Intellamatic® Smart Chargers provide the most reliable, feature-rich performance of any chargers made in the US today.

Associated Intellamatic® battery chargers/analyzers have the following features:

- **SAFE for Sealed Lead Acid, AGM, and Gel Cell batteries**
- Polarity-protected and indicated
- Built-in PATENTED diagnostics to detect weak or defective batteries
- Deep discharge recovery of sulfated batteries
- Tests batteries four times during charge cycle
- Intellamatic® Smart Chargers with the DEAD BATTERY OVERRIDE (DBO) feature for extremely low voltage batteries.
- “Safe in Any Weather” operation
- Indicates 80% and 100% state of charge
- Overcharge protection
- Built-in reflash power supply mode
- TWO-year bumper to bumper warranty and THREE-year limited warranty for transformer/rectifier
- DOE Compliant and Energy-Efficient
- Made in USA of US and Global Components



- Model ESS6007B**
- Intellamatic® 12 Volt 40 Amp Charger
 - 130 Amp Crank Assist
 - 45 Amp Power Supply Mode



- Model ESS6008**
- Intellamatic® 12 Volt 60 Amp Charger
 - 270 Amp Crank Assist
 - 70 Amp Power Supply Mode



- Model ESS6008MSK**
- Intellamatic® 12 Volt 60 Amp Charger
 - 270 Amp Crank Assist
 - 70 Amp Power Supply Mode
 - 10/15 Amp Memory Saver Port
 - 12' ODBII Cable and CC6212 Positive Cable Covers