



ESS6011

Model ESS6011

- Intellamatic® 12/24 Volt 70/35 Amp Charger
- 270 Amp Crank Assist at 12V
- 70 Amp Power Supply Mode



MIL6011

Model MIL6011

- Intellamatic® 12/24 Volt 70/35 Amp Charger
- 270 Amp Crank Assist at 12V
- 70 Amp Power Supply Mode
- Quick disconnect DC leads change from standard clamps to 13' cable with NATO plug using Anderson Connector