

ATEC® PORTABLE POWER

ATEC® Model 6256

- KwikStart™ 12 Volt Portable Power and Jump Starter
- CCA: 360A Peak Current: 1700A
- Rated Input Voltage: 120VAC, 60Hz
- Rated Output Voltage: 12VDC
- Battery Status Indicator, Two 12V Vehicle Adaptors, One 5V DC USB Port & LED Work Light
- DC leads - 36" 500A 4GA
- 22Ah AGM battery
- Imported



ATEC® Model 6296

- CCA: 720A Peak Current 3400A
- Rated Input Voltage: 120 VAC, 60Hz
- Rated Output Voltage: 12/24VDC
- Battery Status Indicator, Two 12V Vehicle Adaptors, LED Work Light
- Overcharge Protection & Overload Protector: 15A internal self-recovery
- Reverse Polarity Alarm with on/off Switch
- Heavy duty DC leads - 44" 500A 2GA
- Two 22Ah AGM batteries
- Imported

ATEC® Model MSK6211 – ATEC® BOOSTER PACK KIT

- INCLUDES 6256 KwikStart with Memory Saver Cable (MS6209)

6256

+

MS6209

=

MSK6211