

Bonded Tubing



Technibond® 2 Bore Metric Sizes

Model	OD	ID	Length	Wall Thickness	Bend Radius	Working Pressure @ 75°F	Colors	Stock	Package Weight
2MP-04M-50-01	4mm	2.4mm	50'	0.78mm	6.35mm	200 psi (13,7 Bar)	Black, Clear Blue	✓	0.70 lb
2MP-04M-A-01			10m					✗	0.46 lb
2MP-04M-B-01			20m					LQ	0.92 lb
2MP-04M-C-01			50m					✗	2.30 lb
2MP-04M-D-01			100m					LQ	4.60 lb
2MP-04M-E-01			200m					✗	9.20 lb
2MP-04M-F-01			300m					✗	13.80 lb
2MP-04M-50-02			Light Blue, Clear				50'	✗	0.70 lb
2MP-04M-A-02							10m	✗	0.46 lb
2MP-04M-B-02							20m	✗	0.92 lb
2MP-04M-C-02							50m	✗	2.30 lb
2MP-04M-D-02							100m	✗	4.60 lb
2MP-04M-E-02							200m	✗	9.20 lb
2MP-04M-F-02							300m	✗	13.80 lb
2MP-06M-50-01	6mm	4mm	50'	1.00mm	12.00mm	180 psi (12,4 Bar)	Black, Clear Blue	✓	1.30 lb
2MP-06M-A-01			10m					✗	0.85 lb
2MP-06M-B-01			20m					LQ	1.71 lb
2MP-06M-C-01			50m					LQ	4.28 lb
2MP-06M-D-01			100m					LQ	8.56 lb
2MP-06M-E-01			200m					LQ	17.12 lb
2MP-06M-F-01			300m					✗	25.68 lb
2MP-06M-50-02			Light Blue, Clear				50'	✗	1.30 lb
2MP-06M-A-02							10m	✗	0.85 lb
2MP-06M-B-02							20m	✗	1.71 lb
2MP-06M-C-02							50m	✗	4.28 lb
2MP-06M-D-02							100m	LQ	8.56 lb
2MP-06M-E-02							200m	✗	17.12 lb
2MP-06M-F-02							300m	✗	25.68 lb

✓: Stocked Assembly, LQ Limited Quantities Available, ✗: Non-Stock (Contact ATP)

Note: See Back Cover or Website for Chemical Compatibility

