

Bonded Spirals



Technibond® 4 Bore Spiral, Metric Sizes

Model	OD	ID	Total Turns	Working Length	Compressed Length	Tail Length	Working Pressure @ 75°F	Spiral OD	Colors	Stock	Package Weight
4MPS-04M-05	4mm	2.4mm	5	45cm	24cm	100mm & 100mm	200 psi (13,7 Bar)	24mm	Black, Clear Blue, Light Blue & Clear	×	0.07 lb
4MPS-04M-10			10	75cm	28cm					×	0.10 lb
4MPS-04M-15			15	105cm	32cm					×	0.14 lb
4MPS-04M-20			20	135cm	36cm					×	0.19 lb
4MPS-04M-30			30	194cm	44cm					×	0.25 lb
4MPS-04M-40			40	254cm	52cm					×	0.32 lb
4MPS-06M-05	6mm	4mm	5	58cm	26cm	100mm & 100mm	180 psi (12,4 Bar)	37mm	Black, Clear Blue, Light Blue & Clear	×	0.21 lb
4MPS-06M-10			10	103cm	32cm					×	0.33 lb
4MPS-06M-15			15	145cm	38cm					×	0.42 lb
4MPS-06M-20			20	190cm	44cm					×	0.57 lb
4MPS-06M-30			30	274cm	56cm					×	0.68 lb
4MPS-06M-40			40	360cm	38cm					×	0.91 lb
4MPS-08M-05	8mm	4.7mm	5	60cm	28cm	100mm & 100mm	175 psi (12 Bar)	41mm	Black, Clear Blue, Light Blue & Clear	×	0.32 lb
4MPS-08M-10			10	105cm	36cm					×	0.58 lb
4MPS-08M-15			15	152cm	44cm					×	0.74 lb
4MPS-08M-20			20	198cm	52cm					×	1.03 lb
4MPS-08M-30			30	288cm	68cm					×	1.40 lb
4MPS-08M-40			40	378cm	84cm					×	1.91 lb
4MPS-10M-05	10mm	6.5mm	5	75cm	30cm	100mm & 100mm	150 psi (10,3 Bar)	52mm	Black, Clear Blue, Light Blue & Clear	×	0.58 lb
4MPS-10M-10			10	135cm	40cm					×	1.01 lb
4MPS-10M-15			15	195cm	50cm					×	1.51 lb
4MPS-10M-20			20	258cm	60cm					✓	1.86 lb
4MPS-10M-30			30	376cm	80cm					×	3.25 lb
4MPS-10M-40			40	497cm	100cm					×	3.38 lb
4MPS-12M-05	12mm	8mm	5	97cm	32cm	100mm & 100mm	150 psi (10,3 Bar)	66mm	Black, Clear Blue, Light Blue & Clear	×	1.10 lb
4MPS-12M-10			10	180cm	44cm					×	1.68 lb
4MPS-12M-15			15	265cm	56cm					×	2.65 lb
4MPS-12M-20			20	345cm	68cm					×	3.42 lb
4MPS-12M-30			30	507cm	92cm					×	5.25 lb
4MPS-12M-40			40	673cm	116cm					×	6.99 lb

✓: Stocked Assembly, LQ Limited Quantities Available, ×: Non-Stock (Contact ATP)

Note: See Back Cover or Website for Chemical Compatibility

