

Bonded Spirals



Technibond® 4 Bore Spiral, Fractional Sizes

Model	OD	ID	Total Turns	Working Length	Compressed Length	Tail Length	Working Pressure @ 75°F	Spiral OD	Colors	Stock	Package Weight
4MPS-532-05	0.156" (5/32")	0.093" (3/32")	5	1.80'	9.50"	4" & 4"	240 psi	1.500"	Black, Clear Blue, Light Blue & Clear	×	0.05 lb
4MPS-532-10			10	3.00'	11.12"					×	0.09 lb
4MPS-532-15			15	4.00'	12.62"					×	0.12 lb
4MPS-532-20			20	5.00'	14.25"					×	0.15 lb
4MPS-532-30			30	6.50'	17.50"					×	0.19 lb
4MPS-532-40			40	8.30'	20.62"					×	0.25 lb
4MPS-14-05	0.250" (1/4")	0.156" (5/32")	5	2.50'	10.50"	4" & 4"	180 psi	2.250"	Black, Clear Blue, Light Blue & Clear	×	0.21 lb
4MPS-14-10			10	3.50'	13.00"					×	0.30 lb
4MPS-14-15			15	5.00'	15.50"					×	0.43 lb
4MPS-14-20			20	6.50'	18.00"					×	0.56 lb
4MPS-14-30			30	9.10'	23.00"					×	0.78 lb
4MPS-14-40			40	11.95'	28.00"					×	1.02 lb
4MPS-38-05	0.375" (3/8")	0.250" (1/4")	5	2.50'	11.75"	4" & 4"	150 psi	3.250"	Black, Clear Blue, Light Blue & Clear	×	0.42 lb
4MPS-38-10			10	4.50'	15.50"					×	0.77 lb
4MPS-38-15			15	6.50'	19.25"					×	1.11 lb
4MPS-38-20			20	8.50'	23.00"					✓	1.45 lb
4MPS-38-30			30	12.20'	30.50"					×	2.08 lb
4MPS-38-40			40	16.00'	38.00"					×	2.73 lb
4MPS-12-05	0.500" (1/2")	0.328" (21/64")	5	3.40'	13.00"	4" & 4"	150 psi	4.375"	Black, Clear Blue, Light Blue & Clear	×	1.15 lb
4MPS-12-10			10	6.20'	18.00"					✓	2.07 lb
4MPS-12-15			15	9.00'	23.00"					×	3.03 lb
4MPS-12-20			20	11.50'	28.30"					×	3.89 lb
4MPS-12-30			30	16.80'	38.00"					×	5.64 lb
4MPS-12-40			40	22.30'	48.00"					×	7.49 lb

✓: Stocked Assembly, LQ Limited Quantities Available, ×: Non-Stock (Contact ATP)

Note: See Back Cover or Website for Chemical Compatibility

