

Tubing & Hose



See Note **Metric Sizes**

Value-Tube™ Part Number (Insert Color)	Imbibe™ Part Number (Insert Color)	OD	ID	Length	Wall Thickness	Bend Radius	Working Pressure at 75°F	Package Weight
PE04M/532A_	DWPE04M/532A_	4mm	2.7mm	100'	0.65mm	25.4mm	180 psi (12,4 Bar)	0.60 lb
PE04M/532B_*	DWPE04M/532B_*			250'				1.50 lb
PE04M/532C_	DWPE04M/532C_			500'				3.00 lb
PE04M/532D_	DWPE04M/532D_			1,000'				6.00 lb
PE06MA_	DWPE06MA_	6mm	4mm	100'	1.00mm	31.8mm	150 psi (10,3 Bar)	1.10 lb
PE06MB_*	DWPE06MB_*			250'				2.75 lb
PE06MC_	DWPE06MC_			500'				5.50 lb
PE06MD_	DWPE06MD_			1,000'				11.00 lb
PE08M/516A_	DWPE08M/516A_	8mm	6mm	100'	1.00mm	38.1mm	150 psi (10,3 Bar)	1.50 lb
PE08M/516B_*	DWPE08M/516B_*			250'				3.75 lb
PE08M/516C_	DWPE08M/516C_			500'				7.50 lb
PE08M/516D_	DWPE08M/516D_			1,000'				15.00 lb
PE10MA_	DWPE10MA_	10mm	8mm	100'	1.00mm	51.0mm	125 psi (8,6 Bar)	2.10 lb
PE10MB_*	DWPE10MB_*			250'				5.25 lb
PE10MC_	DWPE10MC_			500'				10.50 lb
PE12MA_	DWPE12MA_	12mm	9mm	100'	1.50mm	63.5mm	100 psi (6,9 Bar)	2.50 lb
PE12MB_*	DWPE12MB_*			250'				6.50 lb
PE12MC_	DWPE12MC_			500'				13.00 lb

Note: * Indicates Non-Stock Packaged Length

Note: See Back Cover or Website for Chemical Compatibility

Note: Note: Until the product transition is complete, order DWPE part numbers if NSF-61® Certification is required. ATP will ship the appropriate product.

