

841XL, three phase, TEFC, 460 volts and 575 volts, C-Face

Hp	RPM	NEMA Frame	Catalog Number	List Price	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
C-Face, foot mounted, 460 volts (continued)											
40	3600	324TSC	CECP84109T-4	13,368	SD8	29.16	587	92.4	460	44	1
	1800	324TC	CECP84110T-4	12,004	SD8	30.66	600	94.1	460	46	1
	1200	364TC	CECP84308T-4	18,298	SD8	33.49	908	94.1	460	49.4	1
50	3600	326TSC	CECP84114T-4	13,881	SD8	29.16	670	93	460	55	1
	1800	326TC	CECP84115T-4	13,816	SD8	30.66	683	94.5	460	57	1
	1200	365TC	CECP84312T-4	21,053	SD8	33.49	925	94.1	460	61.7	1
60	3600	364TSC	CECP84310T-4	19,269	SD8	31.37	899	95	460	65.1	1
	1800	364TC	CECP84314T-4	19,091	SD8	33.49	906	95	460	68	1
75	3600	365TSC	CECP84313T-4	21,587	SD8	31.37	1007	94.5	460	80.7	1
	1800	365TC	CECP84316T-4	21,465	SD8	33.49	1050	95.4	460	85.9	1
C-Face, foot mounted, 575 volts											
1	1800	143TC	CECP83581T-5	1,870	SD8	13.38	71	87.5	575	1.2	1
2	1800	145TC	CECP83587T-5	1,984	SD8	13.38	80	86.5	575	2.3	1
3	1800	182TC	CECP83661T-5	2,584	SD8	16.69	122	89.5	575	3.3	1
5	1800	184TC	CECP83665T-5	2,598	SD8	16.69	131	89.5	575	5.3	1
7 1/2	1800	213TC	CECP83770T-5	3,291	SD8	20.23	211	91.7	575	7.6	1
10	1800	215TC	CECP83774T-5	3,978	SD8	20.23	231	91.7	575	9.8	1
15	1800	254TC	CECP82333T-5	5,446	SD8	25.28	309	92.4	575	14.1	1
20	1800	256TC	CECP82334T-5	5,762	SD8	25.28	357	93	575	18.3	1
25	1800	284TC	CECP84103T-5	8,087	SD8	27.93	444	93.6	575	24	1
30	1800	286TC	CECP84104T-5	9,261	SD8	27.93	487	93.6	575	28	1
40	1800	324TC	CECP84110T-5	12,004	SD8	30.66	670	94.1	575	37	1
50	1800	326TC	CECP84115T-5	13,816	SD8	30.66	663	94.5	575	45	1
C-Face, footless, 460 volts											
1	3600	143TC	VENCP83580T-4	1,548	SD8	12.00	59	84	460	1.3	1, 60
	1800	143TC	VENCP83581T-4	1,671	SD8	12.00	63	87.5	460	1.5	1, 60
1 1/2	3600	143TC	VECP83583T-4	1,812	SD8	14.56	75	85.5	460	2	1
	1800	145TC	VECP83584T-4	1,885	SD8	14.56	76	88.5	460	2.1	1
2	3600	145TC	VECP83586T-4	1,987	SD8	14.56	83	85.5	460	2.5	1
	1800	145TC	VECP83587T-4	1,965	SD8	14.56	79	88.5	460	2.8	1
3	3600	182TC	VECP83660T-4	2,414	SD8	16.69	121	88.5	460	3.4	1
	1800	182TC	VECP83661T-4	2,559	SD8	16.69	117	89.5	460	4.1	1
5	3600	184TC	VECP83663T-4	2,941	SD8	16.69	132	88.5	460	5.7	1
	1800	184TC	VECP83665T-4	2,573	SD8	16.69	128	89.5	460	6.6	1
7 1/2	3600	213TC	VECP83769T-4	3,794	SD8	20.24	179	91.7	460	8.6	1
	1800	213TC	VECP83770T-4	3,241	SD8	20.24	211	91.7	460	9.5	1
10	3600	215TC	VECP83771T-4	4,029	SD8	20.24	225	91	460	11.3	1
	1800	215TC	VECP83774T-4	3,928	SD8	20.24	231	91.7	460	12.2	1
15	3600	254TC	VECP82394T-4	5,349	SD8	25.28	304	91	460	17	1
	1800	254TC	VECP82333T-4	5,215	SD8	25.28	324	92.4	460	17.6	1
20	3600	256TC	VECP84106T-4	6,097	SD8	25.28	319	91.7	460	22	1
	1800	256TC	VECP82334T-4	5,528	SD8	25.28	355	93	460	23	1

(a) See notes on inside back flap.

■ Cast iron frame

Information

General purpose
Single phaseGeneral purpose
Three phase

Severe duty

Large Motors
and Generators

Washdown duty

Explosion proof

Pump

HVAC

Farm duty