

**Stainless steel, three phase, totally phase, C-Face, foot mounted**

Hp	RPM	NEMA Frame	Enclosure	Catalog Number	List Price	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
<b>575 volt</b>												
1/2	1800	56C	TENV	CSSWDM3538-5	2,200	WDS	11.09	37	80	575	0.7	1, 12
3/4	1800	56C	TENV	CSSWDM3542-5	2,277	WDS	11.09	41	82.5	575	0.9	1, 12
1	1800	56C	TENV	CESSWDM3546-5	2,314	WDS	11.09	46	85.5	575	1.2	
	1800	143TC	TEFC	CESSWDM3546T-5	2,348	WDS	13.42	51	87.5	575	1.3	1
1 1/2	3600	56C	TENV	CESSWDM3550-5	2,337	WDS	12.96	50	85.5	575	1.5	
	1800	145TC	TEFC	CESSWDM3554T-5	2,393	WDS	13.42	56	87.5	575	1.7	1
2	3600	145TC	TENV	CESSWDM3555T-5	2,855	WDS	14.60	61	88.5	575	1.9	8
	1800	145TC	TEFC	CESSWDM3558T-5	2,875	WDS	13.42	45	86.5	575	2.3	8
3	3600	145TC	TEFC	CESSWDM3559T-5	3,440	WDS	15.67	73	86.5	575	2.9	1
		182TC	TENV	CESSWDM3610T-5	3,674	WDS	19.82	96	89.5	575	2.8	8
	1800	182TC	TEFC	CESSWDM3611T-5	3,361	WDS	16.82	92	89.5	575	3.3	1
5	3600	184TC	TEFC	CESSWDM3613T-5	3,909	WDS	18.32	106	90.2	575	4.6	
	1800	184TC	TEFC	CESSWDM3615T-5	3,782	WDS	18.32	112	89.5	575	5.2	
7 1/2	3600	213TC	TEFC	CESSWDM3709T-5	4,588	WDS	19.03	129	91	575	6.7	
	1800	213TC	TEFC	CESSWDM3710T-5	4,731	WDS	20.16	139	91.7	575	7.6	
10	3600	215TC	TEFC	CESSWDM3711T-5	5,119	WDS	20.16	154	91.7	575	8.5	1
	1800	215TC	TEFC	CESSWDM3714T-5	5,218	WDS	21.66	185	91.7	575	9.8	1
15	1800	254TC	TEFC	CESSWDM23933T-5	10,283	WDS	24.67	281	92.4	575	14.2	

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.

Information

General purpose  
Single phase

General purpose  
Three phase

Severe duty

Large Motors  
and Generators

Washdown duty

Explosion proof

Pump

HVAC

Farm duty