

Close-coupled pump, three phase, ODP

Hp	RPM	NEMA Frame	Catalog Number	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
Foot mounted, 230/460 (continued)									
30	3600	284JM	EJMM2534T	26.56	309	91.7	230/460	33	1, 30
		284JP	EJPM2534T	29.44	310	91.7	230/460	33	1, 30
	1800	286JM	EJMM2535T	25.94	359	94.1	230/460	35	1, 30
		286JP	EJPM2535T	28.81	370	94.1	230/460	35	1, 30
40	3600	286JM	EJMM2538T	26.56	328	92.4	230/460	45	1, 30
		286JP	EJPM2538T	29.44	329	92.4	230/460	45	1, 30
	1800	324JM	EJMM2539T	27.44	417	94.1	230/460	49	1, 30
		324JP	EJPM2539T	30.31	378	94.1	230/460	47	1, 30
50	3600	324JM	EJMM2542T	26.94	421	93	230/460	58	1, 30
		324JP	EJPM2542T	29.81	424	93	230/460	58	1, 30
	1800	326JM	EJMM2543T	27.94	491	94.5	230/460	57	1, 30
		326JP	EJPM2543T	30.81	500	94.5	230/460	57	1, 30
60	3600	326JM	EJMM2546T	26.94	472	93.6	230/460	68	1, 30
	1800	364JP	EJPM2547T	33.19	565	95	230/460	68	1, 30
75	1800	365JP	EJPM2551T	36.22	597	95	230/460	87	1, 30
Foot mounted, 575 volts									
3	3600	145JM	EJMM3158T-5	14.25	48	85.5	575	3	
	1800	182JM	EJMM3211T-5	16.50	74	89.5	575	3.1	1
5	3600	182JM	EJMM3212T-5	16.50	63	90.2	575	4.5	
	1800	184JM	EJMM3218T-5	18.00	92	89.5	575	5.2	1
7 1/2	3600	184JM	EJMM3219T-5	16.50	77	88.5	575	6.9	1
	1800	213JM	EJMM3311T-5	18.19	120	91	575	7.4	1, 35
10	3600	213JM	EJMM3312T-5	19.31	137	91.7	575	9.2	
	1800	215JM	EJMM3313T-5	18.19	132	91.7	575	10	1
15	3600	215JM	EJMM3314T-5	19.31	131	90.2	575	14	1
Footless, 230/460									
1	1800	143JM	VEJMM3116T	14.43	37	85.5	230/460	1.5	1, 30
1 1/2	1800	145JM	VEJMM3154T	15.43	43	86.5	230/460	2.2	1, 30
2	1800	145JM	VEJMM3157T	15.43	46	86.5	230/460	2.9	1, 30
3	3600	145JM	VEJMM3158T	14.25	48	85.5	230/460	3.8	1, 30
	1800	184JM	VEJMM3211T	18.06	74	89.5	230/460	4.2	1, 30
5	3600	182JM	VEJMM3212T	16.66	63	86.5	230/460	6	1, 30
	1800	184JM	VEJMM3218T	19.56	84	89.5	230/460	6.6	1, 30
7 1/2	3600	184JM	VEJMM3219T	18.04	77	88.5	230/460	8.6	1, 30
	1800	213JM	VEJMM3311T	19.78	125	91	230/460	9.6	1, 30
10	3600	213JM	VEJMM3312T	18.19	121	89.5	230/460	12	1, 30
	1800	215JM	VEJMM3313T	22.41	165	91.7	230/460	12	1, 30
15	3600	215JM	VEJMM3314T	18.69	131	90.2	230/460	17.5	1, 30
Footless, 575 volts									
1	1800	143JM	VEJMM3116T-5	15.43	44	86.5	575	1.1	
1 1/2	1800	145JM	VEJMM3154T-5	16.31	51	86.5	575	1.6	
2	1800	145JM	VEJMM3157T-5	16.31	52	86.5	575	2.1	
3	1800	182JM	VEJMM3211T-5	18.06	74	89.5	575	3.1	
5	1800	182JM	VEJMM3218T-5	18.06	77	89.5	575	5.2	

(a) See notes on inside back flap.