

Inverter-Duty[®], three phase, ODP, C-Face, foot mounted, with internal AEGIS[®] bearing protection ring

Hp	RPM	NEMA Frame	Catalog Number	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
230/460 volt continued									
50	3600	324TSC	CEM2542T-G	25.69	392	93	230/460	56	8, 30
	1800	326TC	CEM2543T-G	27.69	497	94.5	230/460	57	8, 30
60	3600	326TSC	CEM2546T-G	30.69	616	95	230/460	68	8, 30
	1800	364TC	CEM2547T-G	30.69	565	95	230/460	68	8, 30
75	3600	364TSC	CEM2549T-G	33.72	750	95	230/460	87	8, 30
	1800	365TC	CEM2551T-G	33.72	597	95	230/460	85	8, 30
100	3600	365TSC	CEM2550T-4G	36.97	898	95.4	460	115	8, 30
	1800	404TC	CEM2555T-4G	36.97	898	95.4	460	115	8, 30

(a) See notes on inside back flap.