

U-frame, three phase, TEFC

3/4 thru 20 Hp

IP54



Features:

- Fan cooled
- High performance ball bearings
- Heavy-gauge steel and cast-iron frames
- Exxon Polyrex™ EM grease
- U-Frame mounting dimensions

Applications:

- Pumps
- Compressors
- Fans
- Conveyors
- Machine tools

Hp	RPM	NEMA Frame	Catalog Number	List Price	Disc. Sym.	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
Totally enclosed foot mounted											
3/4	900	184	M3602	2,114	DPL	14.64	51	72	230/460	1.6	1, 30
	1800	182	EM3603	1,788	DPL	13.76	38	85.5	230/460	1.5	1, 30
1	1200	184	EM3604	2,279	DPL	13.76	41	82.5	230/460	1.8	1, 30
	1800	184	EM3606	1,821	DPL	13.76	41	86.5	230/460	2.2	1, 30
1 1/2	1200	184	EM3607	2,435	DPL	15.69	72	87.5	230/460	2.4	1, 30
	1800	184	EM3609	1,922	DPL	13.76	45	86.5	230/460	2.9	1, 30
2	1200	213	EM3712	2,752	DPL	18.17	97	88.5	230/460	3.5	1, 30
	900	215	EM3702	4,286	DPL	18.63	111	85.5	230/460	3.5	1, 30
	3600	184	EM3610	1,923	DPL	14.64	50	86.5	230/460	3.6	1, 30
3	1800	182	EM3611	2,001	DPL	15.69	70	89.5	230/460	4.2	1, 30
	1200	213	EM3703	2,353	DPL	18.17	70	89.5	230/460	4.2	1, 30
	1800	215	EM3704	2,895	DPL	18.63	132	89.5	230/460	4.6	1, 30
5	3600	213	EM3706	3,272	DPL	18.17	74	88.5	230/460	5.9	1
	1800	215	EM3707	2,964	DPL	18.17	93	89.5	230/460	6.7	1, 30
	1200	254U	EM2275	6,033	DPL	20.82	226	90.2	230/460	7.3	1, 30
7 1/2	3600	215	EM3709	3,300	DPL	18.17	96	89.5	230/460	8.4	1, 30
	1800	254U	EM2237	5,138	DPL	23.03	254	91.7	230/460	9.4	1, 30
	1200	256U	EM2276	7,254	DPL	23.03	295	91	230/460	10.7	1, 30
10	1800	256U	EM2238	6,438	DPL	23.03	252	91.7	230/460	13	1, 30
15	1800	284U	EM2333	8,862	DPL	26.34	315	92.4	230/460	18.1	1, 30
20	1800	286U	EM2334	10,606	DPL	26.34	318	93	230/460	24	1, 30
Totally enclosed, C-Face, footless											
2	1800	184C	VEM3609	2,378	DPL	13.31	45	86.5	230/460	2.9	1, 30
	1200	184C	VEM3614	2,687	DPL	17.18	97	88.5	230/460	3.5	1, 30
3	1800	184C	VEM3611	2,458	DPL	15.68	70	89.5	230/460	4.2	1, 30
5	3600	184C	VEM3613	2,208	DPL	15.68	74	88.5	230/460	5.9	1
	1800	184C	VEM3615	2,806	DPL	17.18	93	89.5	230/460	6.7	1, 30

(a) See notes on inside back flap.

■ Cast iron frame

Definite purpose
 Unit Handling
 Brake
 50 Hertz
 Variable Speed AC
 DC
 Accessories
 Service
 Grinders
 Motor Mod