

Pump motor

Jet pump, three phase, ODP 1/3 thru 3 Hp

IP23



Features:

- Corrosion resistant stainless steel shaft extension
- Slotted opposite DE shaft for easy installation
- Dynamically balanced rotor to reduce noise and increase bearing life
- Optimized airflow design providing higher horsepower in a smaller package

Applications:

- HVAC pumps
- Swimming pool pumps
- General purpose pumps

Hp	RPM	NEMA Frame	Catalog Number	"C" Dim.	Aprx. Wt. (lb)	Full Load Efficiency	Voltage	Full Load Amps	Notes (a)
Footless									
1/3	3600	56J	JM3006	11.72	19	62	230/460	0.8	30
1/2	3600	56J	JM3107	11.72	21	70	230/460	1.2	30
	1800	56J	JM3108	11.85	23	74	230/460	1	30
3/4	3600	56J	JM3111	11.72	23	74	208-230/460	1.5	
	1800	56J	JM3112	12.34	27	75.5	208-230/460	1.5	
1	3600	56J	JM3115	12.34	32	77	230/460	1.6	30
	1800	56J	JM3116	13.22	30	78.5	208-230/460	1.7	1
1 1/2	3600	56J	JM3120	13.22	30	74	230/460	2.2	30
	1800	56J	JM3154	13.72	34	77	208-230/460	2.8	
2	3600	56J	JM3155	13.72	35	82.5	230/460	2.7	30
3	3600	56J	JM3158	13.72	42	80	208-230/460	4	
Foot mounted									
1/3	1800	56J	CJM3104	11.85	22	68	230/460	0.8	30
1/2	3600	56J	CJM3107	11.72	22	70	230/460	1.2	30
	1800	56J	CJM3108	11.72	24	74	230/460	1	30
3/4	3600	56J	CJM3111	11.72	28	74	208-230/460	1.5	
	1800	56J	CJM3112	12.34	27	75.5	208-230/460	1.5	
1	3600	56J	CJM3115	12.34	29	77	230/460	1.6	30
1 1/2	3600	56J	CJM3120	13.22	31	81.5	230/460	2	30
2	3600	56J	CJM3155	13.72	34	82.5	230/460	2.7	30
3	3600	56J	CJM3158	13.74	41	80	208-230/460	4	

(a) See notes on inside back flap.

All above ratings can be UL 1081 compliant through MOD Express®.

See M30A in the MOD Express program section of this catalog for more details.