

Three phase, totally enclosed, C-Face, footless

1/3 thru 10 Hp

IP55



Features:

- 300 series stainless steel hardware
- Neoprene gaskets
- Double sealed ball bearings
- Lip and V-Ring seal on DE
- White epoxy, corrosion resistant finish
- Stainless steel shaft extension
- 3 year warranty

Applications:

- Food processing
- Wet environment
- Conveyors
- Packaging
- Pumps and wastewater

| Hp | RPM | NEMA Frame | Enclosure | Catalog Number | List Price | Disc. Sym. | "C" Dim. | Aprx. Wt. (lb) | Full Load Efficiency | Voltage | Full Load Amps | Notes (a) |
|-------|------|------------|-----------|-------------------|------------|------------|----------|----------------|----------------------|-------------|----------------|-----------|
| 1/3 | 1800 | 56C | TENV | VWDM3534 | 855 | WDW | 11.06 | 33 | 75.5 | 208-230/460 | 0.7 | 1, 12 |
| | | 56C | TENV | VEWDM3538 | 1,429 | WDW | 11.06 | 32 | 84 | 230/460 | 0.9 | 1, 30 |
| 1/2 | 1800 | 56C | TEFC | VFWM3538 | 1,116 | WDW | 12.24 | 29 | 80 | 230/460 | 0.8 | 1, 12, 30 |
| | | 56C | TENV | VWDM3538 | 1,069 | WDW | 11.06 | 29 | 80 | 230/460 | 0.8 | 1, 12, 30 |
| 3/4 | 1800 | 56C | TENV | VEWDM3542 | 1,573 | WDW | 11.06 | 32 | 84 | 230/460 | 1.1 | 1, 12, 30 |
| | | 56C | TEFC | VFWM3542 | 1,207 | WDW | 12.24 | 31 | 78.5 | 230/460 | 1.4 | 1, 12, 30 |
| | | 56C | TENV | VWDM3542 | 1,161 | WDW | 11.06 | 33 | 80 | 230/460 | 1.2 | 1, 12 |
| | | 56C | TEFC | VEFWM3546 | 1,749 | WDW | 12.22 | 38 | 85.5 | 230/460 | 1.5 | 1, 30 |
| 1 | 1800 | 56C | TENV | VEWDM3546 | 1,703 | WDW | 12.06 | 40 | 85.5 | 230/460 | 1.5 | 1, 30 |
| | | 143TC | TEFC | VEFWM3546T | 1,762 | WDW | 12.30 | 36 | 85.5 | 230/460 | 1.5 | 1, 30 |
| | | 143TC | TENV | VEWDM3546T | 1,716 | WDW | 12.12 | 40 | 85.5 | 230/460 | 1.5 | 1, 30 |
| | | 56C | TENV | VEWDM3554 | 1,828 | WDW | 12.94 | 48 | 86.5 | 230/460 | 2.1 | 30 |
| 1 1/2 | 1800 | 145TC | TEFC | VEFWM3554T | 1,890 | WDW | 13.28 | 43 | 86.5 | 230/460 | 2.2 | 1, 30 |
| | | 145TC | TENV | VEWDM3554T | 1,843 | WDW | 13.00 | 48 | 86.5 | 230/460 | 2.1 | 30 |
| 2 | 1800 | 56C | TEFC | VEWDM3558 | 1,945 | WDW | 13.22 | 46 | 86.5 | 230/460 | 2.9 | 1, 30 |
| | | 145TC | TEFC | VEWDM3558T | 1,983 | WDW | 13.28 | 47 | 86.5 | 230/460 | 2.9 | 1, 30 |
| | 3600 | 56C | TEFC | VEWDM3559 | 2,253 | WDW | 14.12 | 50 | 86.5 | 230/460 | 3.6 | 1, 30 |
| | | 145TC | TEFC | VEWDM3559T | 2,274 | WDW | 14.17 | 50 | 86.5 | 230/460 | 3.6 | 1, 30 |
| 3 | 1800 | 56C | TEFC | VEWDM3561 | 2,172 | WDW | 15.61 | 73 | 89.5 | 230/460 | 4.2 | 1, 30 |
| | | 145TC | TEFC | VEWDM3561T | 2,197 | WDW | 15.68 | 73 | 89.5 | 230/460 | 4.2 | 1, 30 |
| | | 145TC | TENV | VEWDM3651T | 2,510 | WDW | 15.63 | 91 | 89.5 | 230/460 | 4.1 | 1, 30 |
| | | 182TC | TEFC | VEWDM3611T | 2,491 | WDW | 16.54 | 73 | 89.5 | 230/460 | 4.2 | 1, 30 |
| 5 | 1800 | 184TC | TEFC | VEWDM3615T | 2,824 | WDW | 18.05 | 89 | 89.5 | 230/460 | 6.7 | 1, 30 |
| 7 1/2 | 1800 | 213TC | TEFC | VEWDM3710T | 3,777 | WDW | 19.78 | 151 | 91.7 | 230/460 | 9.5 | 1, 30 |
| 10 | 1800 | 215TC | TEFC | VEWDM3714T | 4,059 | WDW | 21.27 | 165 | 91.7 | 230/460 | 12 | 1, 30 |

(a) See notes on inside back flap.

Red catalog number indicates **NEW** product.