



Working heights to 35'

All in stock with shipments in 2-3 days!

MOBILE VERTICAL SINGLE PERSON LIFT **BMVL-30**



FEATURES

- **300 LBS CAPACITY**
- Manually propelled maintenance lift
- Working heights to 35'
- Compact design for easy storage
- 29x56 base allows lift to roll through standard doorways
- Easy to use outriggers extend from base to provide excellent stability
- 12 Volt DC Power (raise and lower)

MOBILE VERTICAL LIFT • MANUALLY PROPELLED LIFT							
Model Number	Working Height	Platform Height		Platform W" x L"	Footprint W" x L"	Stowed Height	Weight Lbs
		Max	Min				
BMVL-30	35'	30'	10"	24" x 27"	29" x 56"	78"	950
ADDITIONAL INFORMATION							
Outriggers mounted permanently to the unit, swing out, and are electrically interlocked for safe operations. Outrigger footprint - 64" x 74"							

DRIVABLE VERTICAL MAST LIFT **DVML-18**



Cantilevered Platform Extends 21"



FEATURES

- **330 LBS CAPACITY**
- **24' Working Height**
- **Drivable At All Heights**
- **Non-marking Tires**
- Compact Footprint only 30" x 62"
- Standard Platform 24" x 25"
- Cantilever Extension 21"
- Weight 2430 lbs.
- Orange Powder Coat
- 12 Volt DC Power

DRIVABLE VERTICAL MAST LIFT							
Model Number	Working Height	Platform Height		Platform W" x L"	Footprint W" x L"	Stowed Height	Weight Lbs
		Max	Min				
DVML-18	24'	18'	25"	24" x 25"	30" x 62"	78"	2430