

MANUALLY PROPELLED ADJUSTABLE HEIGHT TANK TOP LIFTS

FEATURES:

- Adjustable work heights
- Provides easy access to tank trucks, railroad cars & other cantilevered applications
- Great for clearing snow and ice off tops of trailers
- Manually propelled for use on hard level surfaces
- 48" long cantilevered platform
- Hydraulic hand pump raises & lowers cantilevered platform
- Open serrated grating steps and deck tread.
- Slip resistant climbing rungs
- 28"W x 60"L base, fixed outriggers spread to 69"
- Full rails on both sides, gates at each end of platform
- 2 swivel & 2 rigid 8" casters for use on hard surfaces
- Two adjustable stabilizing jacks secure lifts to ground
- Fixed platform heights available
- Gray coat finish (Standard) Powder

OPTIONAL ACCESSORIES


- AC electric power
- DC electric power
- Air-Hydraulic power
- Tool Tray
- Fluorescent tube holder
- Platform duplex receptacle
- Removable 30" extension rail
- Safety Orange Powder Coat**
- For outdoor applications primer undercoat

**New
Sizes!**

Three power options:

- Plug in 120V AC w/thermal overload protection
- Independent 12V DC deep cycle system with battery, charger and double solenoid for added safety
- Air hydraulic power requiring 90 CFM with 90 PSI pressure

Shown with optional
Safety Orange
finish & 30"
extension
railing



**300 lb.
Capacity**

Model Number	Platform Height		Platform L" x W"	Underclearance Height	Weight Lbs.
	Max	Min			
TT-913	13' 8"	9' 4"	48" x 24"	Adjustable 9' - 13'	1525
TT-913F	13' 8"	9' 4"	48" x 24"	Non-Adjustable 9' - 13'	1450
TT-7-11	11' 8"	7' 4"	48" x 24"	Adjustable 7' to 11'	1450
TT-11-15	15' 8"	11' 4"	48" x 24"	Adjustable 11' to 15'	1625

TELESCOPING HYDRAULIC MAINTENANCE LIFTS MR SERIES

- **500 LB. COMBINED TWO PERSON CAPACITY**
- **Working heights to 34'**
- **Three power options:**
 - Convenient plug in 120V AC
 - Independent 12V DC deep cycle system with battery and charger
 - Air hydraulic power requiring 90 CFM with 90 PSI pressure
- Meets ANSI safety standards

**TWO
WORKER
CAPACITY**

**SHOWN IN
OPTIONAL
ORANGE**

**500 lb.
Capacity**

FEATURES:

- Select from maximum platform heights of 15', 19', 24' or 28'
- Roomy 28" x 36" platform
- Accommodates two workers
- Totally enclosed platform with 42" guard rails, midrails & gate; 4" toeboards and non-slip deck
- Built-in ladder with flat, skid resistant treads and grab rails provides access to platform in fully lowered position
- Rails fold for doorway passage and easy storage
- Non-marking 8" casters for easy rolling and maneuverability
- Self-storing outriggers extend from base for maximum stability
- Leveling jacks secure unit to floor and compensate for uneven surfaces



Rolls thru standard doorway

Model Number	Working Height	Platform Height		Weight Lbs.
		Max	Min	
MR-15-AC	21'	15'	6'4"	800
MR-15-DC	21'	15'	6'4"	930
MR-20-AC	25'	19'3"	6'4"	1,000
MR-20-DC	25'	19'3"	6'4"	1,130
MR-24-AC	30'	23'8"	6'7"	1,200
MR-24-DC	30'	23'8"	6'7"	1,330
MR-28-AC	34'	28'	6'10"	1,420
MR-28-DC	34'	28'	6'10"	1,550

OPTIONAL ACCESSORIES

Air-Hydraulic power
Tool Tray
Fluorescent tube holder
Platform duplex receptacle

