

Polypropylene Class 150 ANSI Flanges

FEATURES

- 150 P.S.I. maximum.
- Glass reinforced polypropylene.
- Heavy duty.



150# THREADED ANSI FLANGES			
PART NO	DESCRIPTION	QTY	PRICE
AF100	1" Female Thread ANSI Flange	1	\$12.86
AF150	1½" Female Thread ANSI Flange	1	\$24.68
AF200	2" Female Thread ANSI Flange	1	\$28.80
AF300	3" Female Thread ANSI Flange	1	\$46.02
AF400	4" Female Thread ANSI Flange	1	\$97.27

150# BLIND ANSI FLANGES			
PART NO	DESCRIPTION	QTY	PRICE
AFB100	1" Blind ANSI Flange	1	\$18.20
AFB150	1½" Blind ANSI Flange	1	\$27.85
AFB200	2" Blind ANSI Flange	1	\$34.61
AFB300	3" Blind ANSI Flange	1	\$60.86
AFB400	4" Blind ANSI Flange	1	\$106.31

ANSI FLANGE GASKETS			
PART NO	DESCRIPTION	QTY	PRICE
AF100G	1" ANSI Flange EPDM Gasket	1	\$4.89
AF100GV	1" ANSI Flange FKM (viton type) Gasket	1	\$46.87
AF150G	1½" ANSI Flange EPDM Gasket	1	\$8.25
AF150GV	1½" ANSI Flange FKM (viton type) Gasket	1	\$59.45
AF200G	2" ANSI Flange EPDM Gasket	1	\$8.95
AF200GV	2" ANSI Flange FKM (viton type) Gasket	1	\$87.42
AF300G	3" ANSI Flange EPDM Gasket	1	\$10.01
AF300GV	3" ANSI Flange FKM (viton type) Gasket	1	\$115.41
AF400G	4" ANSI Flange EPDM Gasket	1	\$12.39
AF400GV	4" ANSI Flange FKM (viton type) Gasket	1	\$168.57



ANSI Flange Gasket