

## FDA CAM LEVER COUPLINGS

•Stainless steel rings, arms and pins •Most complete line of polypropylene FDA couplings available •Versatile — interchangeable with all types of cam lever couplers •Precision molded — insures a uniform and accurate fit •Smooth operating - finger rings are designed for easy opening of cam levers •Operating conditions: 3/8" thru 2" - 100 PSI at -17°C (0°F); 125 PSI at 21°C (70°F); 70 PSI at 66°C (150°F); 3" Cap - 50 PSI Couplings - 75 PSI max •Economic and superior in performance •Standard with FDA EPDM gaskets

Item No.	Size and Part Number			
	3/4"	1"	1-1/2"	2"
A	75A3/4FD	100AFD	150AFD	—
B	75BFD	—	150BFD	300BFD
C	075CFD	—	—	—
D	075DFD	—	150DFD	—
E	075EFD	—	150EFD	—
F	—	100FFD	150FFD	—
PL	—	100125PLFD	150PLFD	200PLFD 300PLFD
CAP	—	150CAPFD	—	300CAPFD

Replacement Gaskets		Item	Description
Part No.	Description	A	Male Adapter - Female Thread
75GFD	3/4" FDA EPDM Gasket	B	Female Coupler - Male Thread
100GW	1" FDA EPDM Gasket	C	Female Coupler - Hose Shank
150GFD	1-1/2" FDA EPDM Gasket	D	Female Coupler - Female Thread
200GFD	2" FDA EPDM Gasket	E	Male Adapter - Hose Shank
300GFD	3" FDA EPDM Gasket	F	Male Adapter - Male Thread
		PL	Plug for Female Coupler
		CAP	Cap for Male Adapter



## BANJO POLYPROPYLENE CAM LEVER COUPLING FEATURES:

•Stainless steel rings, arms and pins •Most complete line of polypropylene couplings available •Interchangeable with all types of cam lever couplers •Precision mold insures a uniform and accurate fit •Polypropylene is glass filled for rugged strength and durability •Finger rings are designed for easy opening of cam levers •Economic and superior in performance •Standard with EPDM gaskets

Operating Conditions	
3/8" thru 2"	100 PSI at -18°C 125 PSI at 21°C 70 PSI at 66°C
2-1/2", 3" and 4" Cap Couplings	50 PSI 75 PSI max

## GREENLEAF CAMLOCK COUPLINGS FEATURES:

•Made to an industry standard and will interchange with all cam lever coupler brands and materials made to the universal specification •Glass filled polypropylene •EPDM Gaskets •Safety Versions come with exclusive cam lever locking mechanism. This mechanism helps reduce the possibility of unintentional opening of the cam levers during use, which could result in personal injury and costly spills.

Max. Operating Pressure	
1/2" thru 2"	125 PSI at 21°C 3" and 4" 75 PSI at 21°C

### SERIES A - MALE ADAPTER X FNPT



Banjo Part No.	GreenLeaf Part No.	Size
<b>Straight</b>		
75A3/8	—	3/8"
75A1/2	G050A	1/2"
75A3/4	G075A	3/4"
100A	G100A	1"
125A	G125A	1-1/4"
150A	G150A	1-1/2"
150125A	G150125A	1-1/2" x 1-1/4"
200A	G200A	2"
—	G300200A	3" x 2"
300A	G300A	3"
400A	G400A	4"
<b>90° Elbow</b>		
150A90	G150A90	1-1/2"
200A90	G200A90	2"

### SERIES B - FEMALE COUPLER X NPT



Banjo Part No.	GreenLeaf Safety Part No.	GreenLeaf Part No.	Size
<b>Straight</b>			
75B1/2	SAF050B	G050B	1/2"
75B3/4	SAF075B	G075B	3/4"
100B	SAF100B	G100B	1"
125B	SAF125B	G125B	1-1/4"
150B	SAF150B	G150B	1-1/2"
150125B	—	G150125B	1-1/2" x 1-1/4"
200B	SAF200B	G200B	2"
300B	SAF300B	G300B	3"
303B*	—	—	—
400B*	—	G400B	4"
<b>90° Elbow</b>			
200B90	—	—	2"

\*Comes with 3 arms

### SERIES C - FEMALE COUPLER X HOSE SHANK



Banjo Part No.	GreenLeaf Safety Part No.	GreenLeaf Part No.	Size
<b>Straight</b>			
050C	SAF050C	G050C	1/2"
075C	SAF075C	G075C	3/4"
100C	SAF100C	G100C	1"
125C	SAF125C	G125C	1-1/4"
150C	SAF150C	G150C	1-1/2"
150125C	—	G150125C	1-1/2" x 1-1/4"
200C	SAF200C	G200C	2"
300C	SAF300C	G300C	3"
303C*	—	—	—
400C*	—	G400C	4"
<b>90° Elbow</b>			
150C90	—	G150C90	1-1/2"
200C90	—	G200C90	2"

\*Comes with 3 arms

### SERIES D - FEMALE COUPLER X FNPT



Banjo Part No.	GreenLeaf Safety Part No.	GreenLeaf Part No.	Size
<b>Straight</b>			
075D3/8	—	—	3/8"
050D	SAF050D	G050D	1/2"
075D	SAF075D	G075D	3/4"
100D	SAF100D	G100D	1"
125D	SAF125D	G125D	1-1/4"
150D	SAF150D	G150D	1-1/2"
150125D	—	G150125D	1-1/2" x 1-1/4"
200D	SAF200D	G200D	2"
—	SAF300200D	G300200D	3" x 2"
300D	SAF300D	G300D	3"
300DB*	—	—	3"
400D**	—	G400D	4"
<b>90° Elbow</b>			
150D90	—	G150D90	1-1/2"
200D90	—	G200D90	2"

\*BSP Female Thread \*\*Comes with 3 arms

### SERIES E - MALE ADAPTER X HOSE SHANK

Banjo Part No.	GreenLeaf Part No.	Size
<b>Straight</b>		
050E	G050E	1/2"
075E	G075E	3/4"
100E	G100E	1"
125E	G125E	1-1/4"
150E	G150E	1-1/2"
150125E	G150125E	1-1/2" x 1-1/4"
200E	G200E	2"
300E	G300E	3"
400E	G400E	4"



### SERIES F - MALE ADAPTER X NPT

Banjo Part No.	GreenLeaf Part No.	Size
<b>Straight</b>		
050F	G050F	1/2"
075F	G075F	3/4"
100F	G100F	1"
125F	G125F	1-1/4"
150F	G150F	1-1/2"
150125F	G150125F	1-1/2" x 1-1/4"
200F	G200F	2"
—	G300200F	3" x 2"
300F	G300F	3"
400F	G400F	4"

