

# PRODUCTS

## 3" Full Port Stubby Valves w/SS

### FEATURES

- Stainless steel ball, handle and stem.
- Locking handle.
- 100 P.S.I.
- PTFE ball seats.
- Glass filled polypropylene.
- FKM (viton type) body seals.
- Stainless steel bolts.



3" FULL PORT STUBBY VALVES W/SS						
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	QTY	PRICE
VSFMT300HSFP	3" FP Male NPT x 3" Male Adapter w/SS Ball, Stem & Handle	100	3"	3"	1	\$357.00

## 3" Full Port Manifold Stubby Valves w/SS

### FEATURES

- Stainless steel ball, handle and stem.
- Locking handle.
- 100 P.S.I.
- PTFE ball seats.
- Glass filled polypropylene.
- FKM (viton type) body seals.
- Stainless steel bolts.



MVSF300HSFP

3" FULL PORT MANIFOLD STUBBY VALVES W/SS						
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	QTY	PRICE
MVSF300HSFP	3" FP Flange x 3" Male Adapter w/ SS Ball, Stem & Handle	100	3"	3"	1	\$357.00



MVSM300HSFP

3" FULL PORT MANIFOLD STUBBY VALVES						
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	QTY	PRICE
MVSM300HSFP	3" FP NPT x 3" Male Flange w/SS Ball, Stem & Handle	100	3"	3"	1	\$357.00



MVS300HSFP

3" FULL PORT MANIFOLD STUBBY VALVES W/SS						
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	QTY	PRICE
MVS300HSFP	3" FP Flange x 3" FP Flange w/ SS Ball, Stem & Handle	100	3"	3"	1	\$357.00