

# 3-Way Poly Ball Valves

## FEATURES

- Stainless steel bolts.
- Precision molded in polypropylene. Polypropylene is reinforced with fiberglass for additional strength.
- Self-aligning ball moves freely against the PTFE seats for smooth operation.
- Ball is diamond turned, after molding, to make it spherically perfect, which provides precise contact between ball and seats.
- PTFE self-lubricating stem bushings and seats.
- Maximum operating pressure 100 P.S.I.
- FKM (viton type) seats.



3" WAY BOTTOM LOAD VALVES							
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	HANDLE TYPE	QTY	PRICE
V075BL	3/4" 3-Way Bottom Load Poly Valve	100	3/4"	1"	T	18/box	\$55.62
V100BL	1" 3-Way Bottom Load Poly Valve	100	1"	1"	T	18/box	\$55.62
V125BL	1 1/4" 3-Way Bottom Load Poly Valve	100	1 1/4"	1 1/2"	T	12/box	\$71.93
V150BL	1 1/2" 3-Way Bottom Load Poly Valve	100	1 1/2"	1 1/2"	T	12/box	\$71.93
V200BL	2" 3-Way Bottom Load Poly Valve	100	2"	2"	Straight	8/box	\$109.77
VT200BL	2" 3-Way Bottom Load Poly Valve	100	2"	2"	T	8/box	\$109.77

**BOTTOM LOAD:** Directional flow, right or left. Valve can be turned off to stop flow.



3" WAY SIDE LOAD VALVES							
PART NO	DESCRIPTION	MAX PSI	PIPE SIZE	OPENING THRU BALL	HANDLE TYPE	QTY	PRICE
V075SL	3/4" 3-Way Side Load Poly Valve	100	3/4"	1"	Straight	18/box	\$55.62
V100SL	1" 3-Way Side Load Poly Valve	100	1"	1"	Straight	18/box	\$55.62
VT100SL	1" 3-Way Side Load Poly Valve	100	1"	1"	T	18/box	\$56.73
V125SL	1 1/4" 3-Way Side Load Poly Valve	100	1 1/4"	1 1/2"	T	12/box	\$71.93
V150SL	1 1/2" 3-Way Side Load Poly Valve	100	1 1/2"	1 1/2"	T	12/box	\$71.93
V200SL	2" 3-Way Side Load Poly Valve	100	2"	2"	Straight	8/box	\$109.77
VT200SL	2" 3-Way Side Load Poly Valve	100	2"	2"	T	8/box	\$109.77

**SIDE LOAD:** Directional flow, right or left. Valve cannot be turned off.