

1/3, 5/8 & 1.1 Cubic Yard TILT TRUCKS - Innovation & value



Smaller-size Tilt Trucks are able to navigate tight spaces and fit through standard doorways. All tilt truck styles include metal handles with the exception of the 5/8 UT & 1.1 UT models. The 1/3 CU-L, 5/8 UT & 1.1 UT models include a single swivel rear caster - all other trucks have two swivel casters each. The molded polyethylene bodies are available in a variety of colors for no extra cost. Standard hinged lids are available for all sizes - Please see details on page 3.

- 18 DIFFERENT STYLES, 6 SIZES TO CHOOSE FROM!
- Seamless bodies molded in polyethylene with heavy duty walls.
- Will not dent, chip, corrode or absorb moisture.
- Steel chassis is all-welded, superior to bolted frames.
- High-quality wheels, casters & hardware are used to ensure that overall wheel and caster capacity is greater than truck rated weight capacity.
- Unique nesting ability due to inset wheels allows for reduced shipping & storage costs, while also protecting walls and door frames from accidental wheel impact.
- Eight different colors available at no extra cost. Custom colors also available!

Model Number	Cubic Yard Capacity	Pound Capacity	Cu. Ft. Capacity	Gallon Capacity	Overall Dimensions	Wheel Type	Caster Type	Shipping Weight	Optional Lid/Weight
1/3 CU-L	1/3	275 lb.	9	67	48" x 26" x 30"	8" rubber on cast steel	1 - 4" medium duty	53 lb.	1/3-LID 12 lb.
1/3 CU-HD	1/3	1200 lb.	9	67	48" x 26" x 30"	8" rubber on cast steel	2 - 4" medium duty	104 lb.	1/3-LID 12 lb.
5/8 UT	5/8	300 lb.	16	123	55.5" x 26.5" x 36"	8" rubber on cast steel	1 - 3" general duty	65 lb.	5/8-LID 13 lb.
5/8 CU-L	5/8	600 lb.	16	123	55.5" x 26.5" x 36"	8" rubber on cast steel	2 - 3" general duty	70 lb.	5/8-LID 13 lb.
5/8 CU-S	5/8	1000 lb.	16	123	55.5" x 26.5" x 37.5"	10" rubber on steel	2 - 4" medium duty	89 lb.	5/8-LID 13 lb.
5/8 CU-HD	5/8	1500 lb.	16	123	55.5" x 26.5" x 37.5"	10" rubber on cast steel	2 - 4" medium duty	117 lb.	5/8-LID 13 lb.
1.1 UT	1.1	600 lb.	29	220	69" x 31.5" x 39.5"	10" rubber on steel	1 - 4" medium duty	85 lb.	1.1-LID 21 lb.
1.1 CU-L	1.1	900 lb.	29	220	69" x 31.5" x 39.5"	10" rubber on steel	2 - 4" medium duty	99 lb.	1.1-LID 21 lb.
1.1 CU-S	1.1	1400 lb.	29	220	69" x 31.5" x 39.5"	10" rubber on cast steel	2 - 4" medium duty	126 lb.	1.1-LID 21 lb.
1.1 CU-HD	1.1	2100 lb.	29	220	69" x 31.5" x 41.5"	12" rubber on cast steel	2 - 6" heavy duty	167 lb.	1.1-LID 21 lb.