

1.7, 2.2 & 3.0 Cubic Yard TILT TRUCKS - Industry leaders!



- Tilt Truck Options:**
- Hinged Lids
 - Locking casters
 - Tow bars and hooks
 - Custom hardware & features
 - Modified body or caster layouts

(See Page 3 for additional options & information)

For over thirty years, Bayhead's high-quality Tilt Trucks have led the industry with the highest weight capacities in a molded truck. With our 3-cubic yard unit available in two styles, Bayhead makes the largest volume capacity too! All three sizes of our large tilt trucks have molded wheel wells, allowing trucks to nest for shipping and helping to protect walls and doorways from impact. Heavy-duty molded bodies are supported by all-welded steel frames with high-quality wheels and casters. The polyethylene bodies are available in a variety of colors for no extra cost. Hinged lids are available for all sizes. Please see other options on page 3.

Model Number	Cubic Yard Capacity	Pound Capacity	Cu. Ft. Capacity	Gallon Capacity	Overall Dimensions	Wheel Type	Caster Type	Shipping Weight	Optional Lid/Weight
1.7 UT	1.7	1000 lb.	50	366	74" x 40" x 50.5"	10" rubber on steel	2 - 4" medium duty	165 lb.	1.7-LID 30 lb.
1.7 CU-S	1.7	1700 lb.	50	366	74" x 40" x 53.5"	12" rubber on cast steel	2 - 6" heavy duty	207 lb.	1.7-LID 30 lb.
1.7 CU-HD	1.7	2200 lb.	50	366	74" x 40" x 53.5"	12" rubber on cast steel	2 - 6" heavy duty	263 lb.	1.7-LID 30 lb.
2.2 UT	2.2	1200 lb.	59	441	74" x 51" x 52.25"	12" rubber on polymer	2 - 5" medium duty	193 lb.	2.2-LID 32 lb.
2.2 CU-S	2.2	2000 lb.	59	441	74" x 51" x 53.5"	12" rubber on cast steel	2 - 6" heavy duty	240 lb.	2.2-LID 32 lb.
2.2 CU-HD	2.2	2500 lb.	59	441	74" x 51" x 53.5"	12" rubber on cast steel	2 - 6" heavy duty	296 lb.	2.2-LID 32 lb.
3.0 CU-S	3.0	2500 lb.	78	585	81" x 56" x 56"	12" rubber on cast steel	2 - 6" heavy duty	298 lb.	3.0-LID 40 lb.
3.0 CU-HD	3.0	2800 lb.	78	585	81" x 56" x 56"	12" rubber on cast steel	2 - 6" heavy duty	350 lb.	3.0-LID 40 lb.